

# VOLTCRAFT

## DATASHEET

Item No.: 2576670

Type designation: LR6 Common: AA

Chemical system: Alkaline

Nominal voltage: 1.5 V


Weight: Approximate 23.8 g

Dimension (mm)

The dimensions shall be in accordance with the below figures both prior to and after the service output test.

Measuring equipment shall be with a minimum accuracy of  $\pm 0.05\text{mm}$ .

/	min	max
$\Phi$	13.7	14.5
A	49.5	50.5
C	7.0	-
F	-	5.5
G	1.0	-



Capacity: 3000 mAh (10 mA, 24 h/d, 20°C, e.v.= 0.8 V)

Operating temperature: -18 °C ~ +50 °C

Recommended temperature: +10°C ~ +25°C

Recommend storage temperature:  $\leq 30^\circ\text{C}$

Shelf lifetime: 7 Years

Type designation: LR03 Common: AAA

Chemical system: Alkaline

Nominal voltage: 1.5 V


Weight: Approximate 12.0 g

Dimension (mm)

The dimensions shall be in accordance with the below figures both prior to and after the service output test.

Measuring equipment shall be with a minimum accuracy of  $\pm 0.05\text{mm}$ .

/	min	max
$\Phi$	9.8	10.5
A	43.5	44.5
C	4.3	-
F	-	3.8
G	0.8	-



Capacity: 1350 mAh (10 mA, 24 h/d, 20°C, e.v.= 0.8 V)

Operating temperature: -18 °C ~ +50 °C

Recommended temperature: +10°C ~ +25°C

Recommend storage temperature:  $\leq 30^\circ\text{C}$

Shelf lifetime: 7 Years

Type designation: 6LR61 Common: 9V

Chemical system: Alkaline


Nominal voltage: 9.0 V

Weight: Approximate 47.0 g


Dimension (mm)

The dimensions shall be in accordance with the below figures both prior to and after the service output test.

Measuring equipment shall be with a minimum accuracy of  $\pm 0.05\text{mm}$ .



/	min	max
H	46.5	48.5
S	-	46.4
F	12.45	12.95
L	24.5	26.5
W	15.5	17.5



Capacity: 550 mAh (35 mA, 24 h/d, 20°C, e.v.= 5.4 V)

Operating temperature: -18 °C ~ +50 °C

Recommended temperature: +10°C ~ +25°C

Recommend storage temperature:  $\leq 30^\circ\text{C}$

Shelf lifetime: 7 Years