

**Safety Data Sheet**  
**According to Regulation (EC) No 1907/2006, Annex II,**  
**Amended by COMMISSION REGULATION (EU) 2015/830,**  
**According to REGULATION (EC) No 1272/2008**

PolyLite™ PETG

Version 1.0

Issue date: 18-06-2019

Revision date: 18-06-2019

SDS Record Number: CSSS-TCO-010-131593

**Section 1 Identification of the substance/mixture and of the company/undertaking**

**1.1 Product identifier:**

Identification on the label/Trade name: PolyLite™ PETG  
Additional identification: Not available  
Identification of the product: See section 3  
Index Number: Not available  
REACH registration No.: Not available

**1.2 Relevant identified uses of the substance or mixture and uses advised against:**

**1.2.1 Identified uses:**

3D Printing Filament.

**1.2.2 Uses advised against:**

Not available.

**1.3 Details of the supplier of the safety data sheet:**

Supplier(Only representative): -  
Supplier(Manufacturer): JF Polymers (Suzhou) Co., Ltd.  
Address: Building 6&7&11, No.2, Hai Cheng Road, Chang Shu Economic & Technological Development Zone, 215513, People's Republic of China  
Contact person(E-mail): Zhenggang Cai (zhenggang.cai@polymaker.com)  
Telephone: +86-512-52058005  
Fax: -

**1.4 Emergency telephone Number:**

+86-512-52058005

Available outside office hours? YES  NO

**Section 2 Hazards Identification**

**2.1 Classification of the substance or mixture:**

**2.1.1 Classification:**

According to REGULATION (EC) No 1272/2008, based on available data, the classification criteria are not met:

REGULATION (EC) No 1272/2008	
Hazard classes/Hazard categories	Hazard codes
Not classified	N/A

**2.2 label elements:**

**Hazard Pictograms:** No hazard pictogram is used.  
**Signal Word(S):** No signal word is used.  
**Hazard Statement:** Not applicable.  
**Precautionary statement:** Not applicable.

**2.3 Other hazards:**

Product name: PolyLite™ PETG

Version #: 1.0

Issue date: 18-06-2019.

Revision date: 18-06-2019.

SDS EU

1 / 6

Not available.

### Section 3 Composition/information on ingredients

**Substance/Mixture:** Substance

**Ingredient(s):** This product does not contain hazardous ingredients above cut-off value according to Regulation (EC) 1272/2008.

### Section 4 First aid measures

#### 4.1 Description of first aid measures:

In all cases of doubt, or when symptoms persist, seek medical attention.

##### 4.1.1 In case of inhalation:

Remove to fresh air. Get medical attention for any breathing difficulty.

##### 4.1.2 In case of skin contact:

May irritate damaged skin. Wash off with soap and plenty of water.

##### 4.1.3 In case of eyes contact:

Immediately flush eyes with plenty of water, lifting upper and lower eyelids occasionally. Get medical attention if irritation persists.

##### 4.1.4 In case of ingestion:

If large amounts were swallowed, give water to drink and get medical advice.

#### 4.2 Most important symptoms and effects, both acute and delayed:

The product is not classified as harmful to human health effect.

#### 4.3 Indication of any immediate medical attention and special treatment needed:

If skin irritation or rash occurs, get medical advice/attention.

### Section 5 Firefighting measures

#### 5.1 Extinguishing media:

**Suitable extinguishing media:** Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

**Unsuitable extinguishing media:** Not available.

#### 5.2 Special hazards arising from the substance or mixture

No specific fire or explosion hazard.

#### 5.3 Advice for firefighters:

Wear self contained breathing apparatus for fire fighting if necessary.

### Section 6 Accidental release measures

#### 6.1 Personal precautions, protective equipment and emergency procedures:

**6.1.1 For non-emergency personnel:** Avoid dust formation.

**6.1.2 For emergency responders:** Wear an appropriate NIOSH/MSHA approved respirator if dust is generated.

#### 6.2 Environmental Precautions:

Do not let large amount of product enter drains.

#### 6.3 Methods and material for Containment and Cleaning up:

Sweep up and shovel. Keep in suitable, closed and properly labelled containers for disposal.

#### 6.4 Reference to other sections:

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for information on disposal.

### Section 7 Handling and storage

## 7.1 Precautions for safe handling:

**7.1.1 Protective measures:** Provide appropriate exhaust ventilation at places where dust is formed.

**7.1.2 Advice on general occupational hygiene:** Do not eat, drink and smoke in work areas. Wash hands after use. Remove contaminated clothing and protective equipment before entering eating areas.

**7.2 Conditions for safe storage, including any incompatibilities:** Keep container closed in a dry place. Avoid dust formation.

**7.3 Specific end use(s):** Not applicable.

## Section 8 Exposure Controls/Personal Protection

### 8.1 Control parameters:

**8.1.1 Occupational exposure limits:** Not available.

**8.1.2 Additional exposure limits under the conditions of use:** Not available.

**8.1.3 DNEL/DMEL and PNEC-Values:** Not available.

### 8.2 Exposure controls:

**8.2.1 Appropriate engineering controls:** Use process enclosures, local exhaust ventilation or other engineering controls to keep worker exposure to airborne contaminants below any recommended or statutory limits. If user operations generate dust, fumes or mist, use ventilation to keep exposure to airborne contaminants below the exposure limit.

#### 8.2.2 Individual protection measures, such as personal protective equipment:

**Eye/face protection:** Safety glasses when eye contact is possible.

**Hand protection:** For prolonged or repeated contact use protective gloves.

**Body protection:** Skin covering working clothes; wear dust-proof overalls if large quantities of dust are generated.

**Respiratory protection:** Respiratory protection is not required. Where protection from nuisance levels of dusts are desired, use type P1 (EN 143) dust masks. Use respirators and components tested and approved under appropriate government standards such as CEN (EU).

**Thermal hazards:** Wear suitable protective clothing to prevent heat.

**8.2.3 Environmental exposure controls:** Avoid discharge into the environment.  
According to local regulations, Federal and official regulations.

## Section 9 Physical and chemical properties

### 9.1 Information on basic physical and chemical properties:

<b>Appearance:</b>	Solid
<b>Colour:</b>	Transparent
<b>Odour:</b>	Not available
<b>Odour threshold:</b>	Not available
<b>pH:</b>	Not available
<b>Melting point/range (°C):</b>	220 °C
<b>Boiling point/range (°C):</b>	Not available
<b>Flash point (°C):</b>	Not available
<b>Evaporation rate:</b>	Not available
<b>Flammability limit - lower (%):</b>	Not available
<b>Flammability (solid, gas):</b>	Not available
<b>Ignition temperature (°C):</b>	Not available
<b>Upper/lower explosive limits:</b>	Not available

Vapour pressure (20°C):	Not available
Vapour density:	Not available
Relative Density:	1.2
Bulk density (kg/m <sup>3</sup> ):	Not available
Water solubility (g/l):	Insoluble in water
n-Octanol/Water (log Po/w):	Not available
Auto-ignition temperature:	Not available
Decomposition temperature:	Not available
Viscosity, dynamic (mPa.s):	Not available
Explosive properties:	Not available
Oxidising properties:	Not available
Molecular Formula:	Not available
Molecular Weight:	Not available

## 9.2. Other information:

Fat solubility(solvent-oil to be specified) etc:	Not available
Surface tension:	Not available
Dissociation constant in water( pKa):	Not available
Oxidation-reduction Potential:	Not available

## Section 10 Stability and reactivity

10.1 Reactivity:	The substance is stable under normal storage and handling conditions.
10.2 Chemical stability:	Stable at room temperature in closed containers under normal storage and handling conditions.
10.3 Possibility of hazardous reactions:	No dangerous reactions known.
10.4 Conditions to avoid:	Incompatible materials.
10.5 Incompatible materials:	Strong oxidizing agents
10.6 Hazardous decomposition products:	Carbon oxide.

## Section 11 Toxicological information

### 11.1 Information on toxicological effects:

Acute toxicity:	
LD50(Oral, Rat):	Not available
LC50(Inhalation, Rat):	Not available
LD50(Dermal, Rabbit):	Not available
Skin corrosion/Irritation:	Not classified
Serious eye damage/irritation:	Not classified
Respiratory or skin sensitization:	Not classified
Germ cell mutagenicity:	Not classified
Carcinogenicity:	Not classified
Reproductive toxicity:	Not classified
STOT- single exposure:	Not classified
STOT-repeated exposure:	Not classified
Aspiration hazard:	Not classified

## Section 12 Ecological information

**12.1 Toxicity:****Acute (short-term) toxicity:**

LC50(96h, Fish): Not available

LC50(48h, Crustacea): Not available

EC50(72h, Algae/aquatic plants): Not available

**Chronic (long-term) toxicity:**

NOEC(Fish): Not available

NOEC(Crustacea): Not available

EC50(Algae/aquatic plants): Not available

**12.2 Persistence and degradability:** Not available.**12.3 Bioaccumulative potential:** Not available.**12.4 Mobility in soil:** Not available.**12.5 Results of PBT and vPvB assessment:** Not available.**12.6 Other adverse effects:** Not available.**Section 13 Disposal considerations**

**13.1 Waste treatment methods:** Any disposal practice must be in compliance with all local and national laws and regulations. Do not dump into any sewers, on the ground, or into any body of water.

**Section 14 Transport information**

	<b>Land transport (ADR/RID)</b>	<b>Inland waterways (ADN)</b>	<b>Sea transport (IMDG)</b>	<b>Air transport (ICAO/IATA)</b>
<b>UN number</b>	Not regulated	Not regulated	Not regulated	Not regulated
<b>UN Proper shipping name</b>	Not regulated	Not regulated	Not regulated	Not regulated
<b>Transport hazard Class(es)</b>	Not regulated	Not regulated	Not regulated	Not regulated
<b>Packing group</b>	Not regulated	Not regulated	Not regulated	Not regulated
<b>Environmental hazards</b>	No	No	No	No
<b>Special precautions for user</b>	See section 2.2	See section 2.2	See section 2.2	See section 2.2
<b>Transport in bulk according to Annex II of Marpol and the IBC Code</b>	Not regulated	Not regulated	Not regulated	Not regulated

**Section 15 Regulatory information****15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture:**

Relevant information regarding authorization: Not applicable.

Relevant information regarding restriction: Not applicable.

**Other EU regulations:** Employment restrictions concerning young person must be observed.  
For use only by technically qualified individuals.

**Other National regulations:** Not applicable**15.2 Chemical safety assessment** YES  NO

## Section 16 Other information

### 16.1 Indication of changes:

Version 1.0 Amended by (EU) 2015/830

### 16.2 Abbreviations and acronyms:

ADR: European Agreement concerning the International Carriage of Dangerous Goods by Road

RID: Regulation for rail International transportation of Dangerous goods

ADN: European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways

IMDG: Code international maritime dangerous goods code

ICAO: International Civil Aviation Organization

IATA: International Air Transport Association

LC50: median lethal concentration

EC50: The effective concentration of substance that causes 50% of the maximum response.

NOEC: No Observed Effect Concentration

DNEL: derived no-effect level

PNEC: predicted no-effect concentration

### 16.3 Key literature references and sources for data

ECHA Registered substances data

### 16.4 Training instructions:

Not applicable.

### 16.5 Further information:

This information is based upon the present state of our knowledge. This SDS has been compiled and is solely intended for this product.

### 16.6 Notice to reader:

Employers should use this information only as a supplement to other information gathered by them, and should make independent judgment of suitability of this information to ensure proper use and protect the health and safety of employees. This information is furnished without warranty, and any use of the product not in conformance with this Safety Data Sheet, or in combination with any other product or process, is the responsibility of the user.

Author: Hangzhou C&K Testing Technic Co.,Ltd Website:www.cirs-ck.com Tel:0571-89900715 Email:testing@circs-group.com

