

VOLTCRAFT – TOP PERFORMANCE IN EVERY WAY

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

VC40 SOCKET TESTER



N° 2633264

With the VC40 socket tester, a simple and fast test of safety sockets, cable drums and extension cables for correct connection is possible. The VC 40 socket tester is capable of checking the socket for correct polarity and displays wiring errors by means of an optical display. In addition, tests can be carried out to determine unwanted voltages between earthing and neutral and residual current (RCD) voltages. The device is solidly built, yet compact and lightweight.

FEATURES:

Automatic polarity test of safety sockets // subsequent residual current test (RCD) and test for an unacceptable voltage drop between earthing and neutral conductor at the touch of a button //

EQUIPMENT:

Safety plug with earthing (Type E+F (CEE 7/7)) // Acoustic and visual display // Interpretation assistance on the device // Isolated control buttons //

TECHNICAL DATA:

| | |
|----------------------------------|---|
| Measuring voltage | 230 V/AC 50Hz |
| Power consumption | 11 mA |
| RCD Test: | |
| Rated current | 30 mA +/- 5% (at 230 V/AC, 50 Hz) |
| Test time | max. 300 ms |
| Neutral earthing | 50 V +/- 10% rms |
| Earthing test | 156 g |
| Threshold | 50 V +/- 10% rms (for resistors < 100 kΩ) |
| Reaction time | 100 ms |
| Operating conditions temperature | +5 to +40 °C (+41 to +104 °F) |
| humidity | < 80% relative, non-condensing |
| Storage conditions temperature | -20 to +60 °C (-4 to +140 °F) |
| humidity | < 80% relative, non-condensing |
| Dimensions (W x H x D) | 69 x 67 x 32mm |
| Weight | 80 g |



PACKAGE CONTENTS:

Socket tester VC40 // Operating instructions //

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

Copyright 2022 by Conrad Electronic SE.

*2633264_V1_1122_02_dm_ds_en