



Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **Power Resistor**

Passive Component Dimensions: **9.5 x 3.6 mm**

Number of Terminations: **2**

Packaging Method: **Ammo Packed**

Passive Component Tolerance: **5 %**

## Features

### Product Type Features

Product Type	Fixed Resistor
Resistor Type	Power Resistor
Element Type	Carbon Composition

### Configuration Features

Number of Resistors	1
---------------------	---

### Electrical Characteristics

Voltage Rating	350 V
Passive Component Tolerance	5 %
Resistance Class	Up to 1k $\Omega$
Resistance Value	330 $\Omega$
Power Rating	.5 W

### Body Features

Passive Component Lead Type	Axial-Leaded
-----------------------------	--------------

### Termination Features

Number of Terminations	2
Passive Component Termination Material Type	Tinned Copper Leads

### Dimensions

Passive Component Dimensions	9.5 x 3.6 mm
------------------------------	--------------

### Usage Conditions

Operating Temperature Range	-55 – 125 °C
Temperature Coefficient	-600 – 200 ppm/°C

### Packaging Features

Packaging Method	Ammo Packed
------------------	-------------

### Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts

 <p>TE Part # 1-1625876-7 CBT 1/2 5% 1R0</p>	 <p>TE Part # 2-1625876-9 CBT 1/2 5% 100R</p>	 <p>TE Part # 1625875-5 CBT 1/4 5% 100R</p>	 <p>TE Part # 1-1625875-2 CBT 1/4 5% 1K0</p>
---	--	--	---



TE Part # 3-1625875-1  
CBT 1/4 5% 3R3

### Also in the Series | Neohm CBT



Through-Hole Resistors(8)


### Customers Also Bought




TE Part #1-1462037-6  
IM03JR=IM RELAY 140mW 5V




TE Part #4-2176057-1  
RLP73K 3A R47 1% 1K RL




TE Part #3-1761607-1  
IDC LOW PRO HDR 34P RA LG LAT  
BLUE



TE Part #7-534206-0  
40 MODII VRT DR CE 100/115  
BLUE



TE Part #3-1761606-3  
IDC LOW PRO HDR 40P VERT LG LA



TE Part #3-1761606-1  
IDC LOW PRO HDR 34P VERT LG LA



TE Part #1-1761606-0  
IDC LOW PRO HDR 30P VERT LG LA



TE Part #3-826936-2  
32P AMPMODU II STIFT LEI



TE Part #2-2176349-6  
CRGCO 2512 1K2 1%



## Documents

### Product Drawings

[CBT 1/2 5% 330R](#)

English

### CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_5-1625876-1\\_A.2d\\_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_5-1625876-1\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_5-1625876-1\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[4-1773460-6\\_RESISTIVE\\_SOLUTIONS\\_RAIL](#)

English

[1309350\\_PASSIVE\\_COMPONENT](#)

English

[Carbon Composition Resistors - Type CBT Series](#)

English

[8-1773459-4\\_POWER\\_FILTERING\\_AND\\_RESISTIVE\\_SOLUTIONS\\_FOR\\_ELEVATORS\\_AND\\_ESCALATORS](#)

English