



Type  
Catalog No.

Z-DSV-LN  
248878

### Data for konstruksjonsdokumentasjon iht. IEC/EN 61439

Tekniske data for konstruksjonsdokumentasjon			
Nominell strøm for angivelse av tapseffekt	$I_n$	A	20
Tapseffekt per pol, strømvhengig	$P_{vid}$	W	0
Tapseffekt for driftsmiddelet, strømvhengig	$P_{vid}$	W	2
Tapseffekt statisk, uavhengig av strøm	$P_{vs}$	W	0
Avleveringskapasitet for tapseffekt	$P_{ve}$	W	0
Omgivelsestemperatur ved drift min.		°C	-40
Omgivelsestemperatur ved drift maks.		°C	60
			0

### Tekniske data etter ETIM 6.0

Devices for distribution board-/surface mounting (EG000062) / Main switch for distribution board (EC001545)			
Electric engineering, automation, process control engineering / Electrical installation, device / Modular serial built-in device for electrical circuit distributors / Main switch for distribution board (ec1@ss8.1-27-14-23-01 [AFZ813011])			
Switching function			Other
Number of normally open contacts			0
Number of normally closed contacts			0
Number of change-over contacts			1
Number of poles			0
Nominal rated current		A	20
Nominal rated voltage		V	690
Min. rated voltage		V	440
Rated switching capacity		kA	0
Short-circuit breaking capacity ( $I_{cw}$ )		kA	10
Voltage type			AC
Forced segregation (according to DIN VDE 0113)			No
With signal lamp			No
Colour calotte			Not applicable
Lamp type			Not applicable
Lamp socket			Not applicable
Max. lamp power		W	0
Width in number of modular spacings			3
Built-in depth		mm	60
Degree of protection (IP)			IP20