10.1

2.1



# Model number

## VAA-2E2A-CB10-SJ/E2J-FL

CB10 safety module, 2 safety-related inputs and 2 conventional electronic outputs

### **Features**

- Connection of contact safety switches, e.g. EMERGENCY STOP button
- Applications up to Cat. 4, PLe / SIL3
- Modular safety solution
- Ultra-compact enclosure

### **Function**

The VAA-2E2A-CB10-SJ/E2J-\* is an AS-Interface safety module with 2 safety-related inputs and two conventional outputs. A twochannel mechanical switch or a single channel mechanical switch each can be connected to the two safety-related inputs. The outputs are conventional electronic nonsafety-related outputs, which can be loaded with 100 mA in total.


The module is suitable for remote connection of switches in very limited space. The onepiece housing provides a degree of protection of IP20.

The connection to the AS-Interface cable as well as to the inputs and outputs takes place via strands with open cable ends.


To indicate the current switching state, an LED is available for each channel, mounted on top of the module. Two status LEDs are used to monitor the AS-Interface communication and indicate whether the module has the address 0.

The module can be used up to Category 4/PL e according to ISO 13849-1, SIL 3 according to EN 62061.

If two single-channel switches are connected, the module can be used up to Category 2/ PL c according to ISO 13849-1, SIL 1 according to EN 62061.



# **Electrical connection**



fa-info@us.pepperl-fuchs.com


Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com



Pepperl+Fuchs Group

www.pepperl-fuchs.com

## Indicating / Operating means



# Technical data

Technical data				
General specifications				
Slave type		Safety-Slave		
AS-Interface specificati	on	V3.0		
Required master specif	ication	≥ V2.1		
UL File Number		E223772		
Indicators/operating m	eans			
LED FAULT		error display; LED re	d	
		red: communication		
LED PWR		AS-Interface voltage		
		green: voltage OK	groon LEB	
		flashing green: addre	ass 0	
LED IN		switching state (input		
LED OUT		Switching state (outp		
		Switching state (outp	ut), 2 LED yellow	
Electrical specification		00 5 01 01/1		
Rated operating voltage	e U <sub>e</sub>	26.5 31.6 V from A	S-Interface (PELV)	
Rated operating current	t l <sub>e</sub>	· ·	uts/outputs)/max. 160 mA	
Protection class		III		
Surge protection			egory III, safe isolated power s	upplies
		(PELV)		
Rated insulation voltage	9	32 V		
Pulse withstand voltage		0.8 kV		
Input				
Number/Type		2 safety-related input	s for mechanical contacts, cro	sed-circuit
миниен туре		2 salety-related input monitored:	s for mechanical contacts, cro	sseu-circuit
			tacts: Up to category 2/PLc in	accordance
			SIL 1 in accordance with IEC 6	
			t: Up to category 4/PLe in acc	
			in accordance with IEC 6206	
Supply		from AS-Interface		1
Supply			4	
Voltage		20 30 V DC pulsed		
Current		input current limited		
_		short-circuit protecte	đ	
Output				
Number/Type		2 conventional electr	onic outputs, PNP , overload a	nd short-cir-
		cuit resistant		
Supply		from AS-Interface		
Voltage		(U <sub>ASI</sub> - 7.0 V) ≤ U <sub>OUT</sub>	·≤U <sub>ASI</sub>	
Current		≤ 100 mA per output		
Directive conformity				
Electromagnetic compa	atibility			
Directive 2014/30/EU	anomy	IEC 62026-2-2012 E	N 61000-6-2:2005 EN 61000-6	8.4.2007 EN
Directive 2014/30/EU		61326-1:2013 E	1 01000-0-2.2005 EN 01000-0	5-4.2007 EN
Machinony Directive		01320-1.2013		
Machinery Directive		EN100 400 40 4 00	5 EN 100 100 10 0 0010	
Directive 2006/42/EC			5 EN ISO 13849-2:2012	
		EN 62061:2005 + AC	22010 + A1:2013 + A2:2015	
Standard conformity				
Degree of protection		EN 60529:2000		
Fieldbus standard		EN 62026-2:2013	EN 62026-2:2013	
Electrical safety		IEC 61140:2009		
Emitted interference		EN 61000-6-4:2007		
AS-Interface		EN 62026-2:2013		
Noise immunity			N 61326-3-1:2017 EN 61000-6	3-2.2005
Functional safety			5 EN ISO 13849-2:2012	5 2.2000
i unctional salety			22010 + A1:2013 + A2:2015	
B		LN 02001.2003 + AC	.2010 + A1.2013 + A2.2015	
Programming instruction	ons			
Profile		S-7.B		
IO code		7		
ID code		В		
ID1 code		F		
ID2 code		0		
Data bits (function via	AS-Interface)	input	output	
			· · · · ·	
2 Refer to "General Not	tes Relating to Pepp	erl+Fuchs Product Informa	tion".	
reppen+ruchs Grou		x: +1 330 486 0001	Germany: +49 621 776 4411	Singapor
www.pepperl-fuchs.c	om ta-into@	us.pepperl-fuchs.com	fa-info@de.pepperl-fuchs.com	fa-info@sg.p

# VAA-2E2A-CB10-SJ/E2J-FL

## Accessories

VBP-HH1-V3.0-KIT AS-Interface Handheld with accessory

VAZ-PK-FK-0,2M-V1-W Adapter cable G10 module/hand-held programming device

**PEPPERL+FUCHS** 

# AS-Interface safety module

# VAA-2E2A-CB10-SJ/E2J-FL

D0	dyn. safety code 1	OUT 1	
D1	dyn. safety code 1	OUT 2	
D2	dyn. safety code 2	-	
D3	dyn. safety code 2	-	
Parameter bits (programmable via AS-i)			
P0	not used		
P1	not used		
P2	not used		
P3	not used		
Ambient conditions			
Ambient temperature	-25 70 °C (-13 158 °F)		
Storage temperature	-25 85 °C (-13 185 °F)		
Relative humidity	85 %, noncondensing		
Climatic conditions	For indoor use only		
Altitude	< 5000 m above MSL		
Shock and impact resistance	30 g, 11 ms in 6 spatial directions, 3 shocks 10 g, 16 ms in 6 sp		
·	tial directions, 1000 shocks		
Vibration resistance	0.35 mm 10 57 Hz , 5 g 57 2000 Hz, 10 cycles		
Pollution degree	2		
Mechanical specifications			
Degree of protection	IP20 according to EN 60529		
Connection	200 mm, PVC cable 0.5 mm <sup>2</sup>		
Material			
Contacts	open conductor ends with connector sleeves		
Housing	Polyamide hot-melt adhesive		
Mass	31 g		
Note	This device is maintenance-free. If the device is used in a mar ner not specified by the manufaturer, the protection provided b the device may be impaired.		
Approvals and certificates			
UL approval	Protection class IP20 is not included in the UL approval. The		
	protection class is tested by Pepperl+Fuchs.		
Functional safety related parameters			
Operating mode	1-channel	2-channel	
Safety Integrity Level(SIL)	SIL 1	SIL 3	
	-	DI -	
Performance Level (PL)	PLc	PLe	
Performance Level (PL) Category	PL c Cat. 2	PL e Kat. 4	
	Cat. 2 100 a	Kat. 4 no significant contribution to	
Category	Cat. 2	Kat. 4 no significant contribution to	
Category MTTF <sub>d</sub>	Cat. 2 100 a	Kat. 4 no significant contribution to MTTFd or PFH <sub>d</sub> of the overall	
Category MTTF <sub>d</sub> PFH <sub>d</sub>	Cat. 2 100 a 2,3 x 10 <sup>-7</sup>	Kat. 4 no significant contribution to MTTFd or $PFH_d$ of the overall system	

Safety Instructions If a single-channel switch is used, the module is suitable for use up to category 2/PL c in accordance with ISO 13849-1, or SIL 1 in accordance with EN/IEC 62061. Only tested and certified power supplies with safe isolation may be used to supply power. These power supplies must have PELV voltage in accordance with EN 50295 / IEC 62026-2, and a minimum MTBF of 50 years. The power supplies are designed to exclude a short circuit between the primary and secondary sides.

Mounting Instructions You may attach the device to a level mounting surface using the enclosed double-sided adhesive pad.

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Pepperl+Fuchs Group www.pepperl-fuchs.com

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

