




CGS | CGS ES

TE Internal #: 1879103-1

Through-Hole Resistors, Power Resistor, 13 x 5.5 mm, 2 Termination, Taped & Reeled, 5 %, Wire Wound, Resistance Class Up to 1kΩ, 56 Ω, 3 W, CGS ES

[View on TE.com >](#)

Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **Power Resistor**

Passive Component Dimensions: **13 x 5.5 mm**

Number of Terminations: **2**

Packaging Method: **Taped & Reeled**

Passive Component Tolerance: **5 %**

Features

Product Type Features

| | |
|---------------|----------------|
| Product Type | Fixed Resistor |
| Resistor Type | Power Resistor |
| Element Type | Wire Wound |

Configuration Features

| | |
|---------------------|---|
| Number of Resistors | 1 |
|---------------------|---|

Electrical Characteristics

| | |
|-----------------------------|-----------|
| Passive Component Tolerance | 5 % |
| Resistance Class | Up to 1kΩ |
| Resistance Value | 56 Ω |
| Power Rating | 3 W |

Body Features

| | |
|-----------------------------|--------------|
| Passive Component Lead Type | Axial-Leaded |
|-----------------------------|--------------|

Termination Features

| | |
|---|---------------------|
| Number of Terminations | 2 |
| Passive Component Termination Material Type | Tinned Copper Leads |

Dimensions

| | |
|------------------------------|-------------|
| Passive Component Dimensions | 13 x 5.5 mm |
|------------------------------|-------------|



Usage Conditions

| | |
|-------------------------|-------------|
| Temperature Coefficient | ±300 ppm/°C |
|-------------------------|-------------|

Packaging Features

| | |
|------------------|----------------|
| Packaging Method | Taped & Reeled |
|------------------|----------------|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|--|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Wave solder capable to 265°C |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

TE Part # 2-1624235-1
ES 3WATT R05 2% T/B


TE Part # 2-1624235-3
ES 3WATT 100R 5% T/R

TE Part # 1624235-1
ES 3WATT 100R 5% T/B

TE Part # 1-1624235-5
ES 3WATT R05 5% T/B

TE Part # 3-1624236-1
ES 6WATT 1K0 5% T/R




TE Part # 1879104-1
ES 1/2WATT 100R 5% T/B




TE Part # 1879287-3
ES 1WATT 15R 5% T/B




TE Part # 1879287-2
ES 1WATT 1R5 5% T/B



TE Part # 1624235-4
ES 3WATT 150R 5% T/B




TE Part # 2-1624235-6
ES 3WATT LONG CASE 39R 5% T/B



TE Part # 1-1624235-1
ES 3WATT 3R3 5% T/B



TE Part # 1-1624235-2
ES 3WATT 47R 5% T/B



TE Part # 1-1624235-6
ES 3WATT R07 5% T/B



TE Part # 1624236-5
ES 5WATT R10 5% T/R




TE Part # 3-1624236-2
ES 6WATT 2R7 5% T/R




TE Part # 3-1624236-4
ES 6 WATT R22 5% T/R

Also in the Series | **CGS ES**



Through-Hole Resistors(17)

Customers Also Bought



TE Part #280377-1
2P AMPMODU II SHRD HDR, RT ANG, TIN



TE Part #63138-1
110 FASTON REC 22-18 AWG TPBR



TE Part #62833-1
MAG-MATE POKE-IN TERM 016TPBR



TE Part #7-1440000-7
OMIH-SH-148L,394



Documents

Product Drawings

[ES 3WATT SM 56R 5%\(52MM TAPING\)](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1879103-1_BA.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1879103-1_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1879103-1_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[4-1773460-6_RESISTIVE_SOLUTIONS_RAIL](#)

English

[1309350_PASSIVE_COMPONENT](#)

English

[High Power Resistors - Type ES Series - Tyco Electronics Passives](#)

English