Science. Applied to Life.™

3M[™] Solus[™] 1000 Series Safety Spectacles

Technical datasheet



Product description

The 3M[™] Solus[™] 1000 is a safety spectacle with:

- Slim frame
- Scotchgard™ Anti-Fog coating
- Optional adjustable headband
- Optional foam or TPE gasket

Key features

- Optical class 1 lens for prolonged use
- ► Single piece ocular lens
- Semi-rimless ocular frame
- Frame colours in either blue/black or green/black
- Scotchgard™ Anti-Fog coating providing protection against fogging and scratching, meeting K and N marking requirements of EN 166
- ► Offers protection against UV radiation
- Optional foam gasket or TPE gasket to give medium energy impact protection when worn with headband
- TPE gasket designed to be worn with 3M[™] Solus[™] 1000 prescription inserts
- Scotchgard™ Anti-Fog coating provides scratch resistance and durability, even after multiple washes
- Can be autoclaved for use in cleanroom environments (based on internal testing)
- Basic weight 26g

Typical applications

These products may be suitable for use in a wide variety of applications including:

- Industrial manufacturing
- Metal working
- Construction
- Food industry
- Pharmaceutical
- General laboratory

Intended use

These products are intended for protection against a variety of hazards including low energy impact (F) when worn as a spectacle with temple arms, or medium energy impact (B) when worn as a goggle with a headband and gasket. These products also provide protection at extremes of temperature -5°C and +55°C (T) in accordance with EN 166:2001.

When worn as a goggle with a headband and TPE gasket these assemble option also provide protection against droplets or splashes of liquid (3) and large dust particles (4), which meet EN 166:2001.

These products also help protect against UV radiation in accordance with EN 170:2002 (clear and amber lenses), and sun glare in accordance with EN 172:1994 (grey and indoor/outdoor lenses).

Product range

3M[™] Solus[™] 1101SGAF-EU, clear polycarbonate lens with Scotchgard[™] coating and Blue/Black frame

3M[™] Solus[™] 1101NSGAF-TSKT-EU, clear polycarbonate lens with Scotchgard[™] coating, Blue/Black frame, with TPE insert and neoprene headband

3M[™] Solus[™] 1101SGAFKT-EU clear polycarbonate lens with Scotchgard[™] coating, Blue/Black frame, with foam insert and headband

3M™ Solus™ 1201SGAF-EU, clear polycarbonate lens with Scotchgard™ coating and Green/Black frame

3M[™] Solus[™] 1201SGAFKT-EU, clear polycarbonate lens with Scotchgard[™] coating, Green/Black frame, with foam insert and headband 3M[™] Solus[™] 1201SGAF-TSKT-EU, clear polycarbonate lens with Scotchgard[™] coating, Green/Black frame, with TPE insert and fabric headband

3M™ Solus™ 1102SGAF-EU, grey polycarbonate lens with Scotchgard™ coating and Blue/Black frame

3M™ Solus™ 1202SGAF-EU, grey polycarbonate lens with Scotchgard™ coating and Green/Black frame

3M™ Solus™ 1103SGAF-EU, amber polycarbonate lens with Scotchgard™ coating and Blue/Black frame

3M™ Solus™ 1203SGAF-EU, amber polycarbonate lens with Scotchgard™ coating and Green/Black frame

3M™ Solus™ 1107SGAF-EU, Indoor/outdoor polycarbonate lens with Scotchgard™ coating and Blue/Black frame

3M™ Solus™ 1207SGAF-EU, indoor/outdoor polycarbonate lens with Scotchgard™ coating and Green/Black frame

3M™ Solus™ 1000S-EU, headband

3M™ Solus™ 1000G-EU, foam gasket

3M™ Solus™ 1000TPE-EU, TPE gasket

3M™ Solus™ 1000RX-EU, RX insert with TPE gasket

Intended use (continued)

The 3M[™] Solus[™] 1000 lenses are also intended to give an enhanced level of protection against fogging and scratching from the Scotchgard[™] coating which meets K rating for anti-scratch (AS) and N rating for anti-fog (AF) as per EN 166:2001.

Sterilisation by autoclaving - limited internal testing has been carried out on samples subjected to 10x, 20x, 30x and 40x automatic cleaning and disinfection and sterilisation by autoclaving at 121°C. Testing was then carried out on the following properties:

- Mechanical performance (BT)
- Anti-fog properties (N)
- Anti-scratch properties (K)
- Optical performance

Based on the internal testing the claims remain valid.

NOTE: Sterilisation by autoclaving was only tested on the safety spectacles (3M[™] Solus 1101SGAF-EU and 3M[™] Solus 1201SGAF-EU). Testing was NOT carried out on the foam insert or headband.

A number of lens options are available for a variety of different applications:

- Clear Good colour recognition and excellent UV protection
- Grey Protection from sunglare
- Amber Enhanced contrast in low light conditions
- Indoor / Outdoor Perfect for workers that move in and out of strong sunlight
- Scotchgard[™] for added protection against fogging and scratching (EN 166 anti-fog (N) and anti-scratch (K))

Use limitation

- Never modify or alter this product
- ► Do not use this product against hazards other than those specified in this document
- ▶ These products are not suitable for grinding or welding
- These products are NOT designed to be worn over prescription spectacles

Standards and approval

These products are type examined by SATRA Technology Europe Ltd, Bracetown Business Park, Clonee, Dublin 15, Dublin, Ireland. Notified Body No. 2777. These products are CE marked to the requirements of the European Regulation (EU) 2016/425.

[GB only]: These products are type examined by SATRA Technology Centre Limited, Wyndham Way, Telford Way, Kettering, Northamptonshire, NN16 8SD, United Kingdom. Approved Body No. 0321.

These products are UKCA marked and meet the requirements of Regulation 2016/425 on personal protective equipment, as amended to apply in GB.

The applicable legislation can be determined by reviewing the Certificate and Declaration of Conformity at www.3M.com/Eye/certs.

Materials listing

Material
Polycarbonate
Polycarbonate
TPE
TPR
Nylon fibre or neoprene
Polycarbonate
Nylon
EVA foam or TPE
Polycarbonate / polyester blend

Marking

The products have demonstrated compliance with the requirements of EN 166:2001 and associated standards and bear the following marks:


Product lens	Lens marking	Frame marking
S1101SGAF-EU	2C-1.2 3M 1 BT K N	EN 166 FT CE
S1201GAF-EU	2C-1.2 3M 1 BT K N	EN 166 FT CE
S1103SGAF-EU	2C-1.2 3M 1 BT K N	EN 166 FT CE
S1203SGAF-EU	2C-1.2 3M 1 BT K N	EN 166 FT CE
S1102SGAF-EU	2C-3 / 5-3.13M1BTKN	EN 166 FT CE
S1202SGAF-EU	2C-3 / 5-3.13M1BTKN	EN 166 FT CE
S1107SGAF-EU	5-1.7 3M 1 BT K N	EN 166 FT CE
S1207SGAF-EU	5-1.7 3M 1 BT K N	EN 166 FT CE
S1000 Foam gasket	-	EN 166 BT CE
S1000 TPE Gasket	-	EN 166 BT 3 4 CE


Explanation of marking

Marking	Description
2C-1.2 (EN 170:2002)	UV protection with good colour recognition. This product conforms to the requirements of the standard, providing UV protection for the complete specified range (210nm – 365nm)
5-1.7 and 5-3.1 (EN 172:1994 (as amended))	Sun-glare protection conforming to the requirements of the standard, providing UV protection for the complete specified range (280nm – 350nm)
1	Optical class
F	Impact protection against high speed particle at low energy (45m/s)
В	Impact protection against high speed particle at medium energy (120m/s)
T	Tested for impact protection at extreme temperature conditions -5°C and +55°C
K	Resistance to surface damage by fine particles
N	Resistance to fogging
3	Protection against droplets and splashes of liquid
4	Protection against large dust particles


User instructions



















IMPORTANT NOTICE

The use of the 3M product described within this document assumes that the user has previous experience of this type of product and that it will be used by a competent professional. Before any use of this product it is recommended to complete some trials to validate the performance of the product within its expected application. All information and specification details contained within this document are inherent to this specific 3M product and would not be applied to other products or environment. Any action or usage of this product made in violation of this document is at the risk of the user.

Compliance to the information and specification relative to the 3M product contained within this document does not exempt the user from compliance with additional guidelines (safety rules, procedures). Compliance to operational requirements especially in respect to the environment and usage of tools with this product must be observed. The 3M group (which cannot verify or control those elements) would not be held responsible for the consequences of any violation of these rules which remain external to its decision and control.

Warranty conditions for 3M products are determined with the sales contract documents and with the mandatory and applicable clause, excluding any other warranty or compensation.

For more information on 3M products and services please contact 3M.

Personal Safety Division 3M United Kingdom PLC 3M Centre Cain Road, Bracknell Berkshire RG12 8HT t: 0870 60 800 60 www.3M.eu/safety

3M Ireland Limited The Iveagh Building Carrickmines Park, Carrickmines D18 X015 Ireland +353 (0)1 280 3555 Please recycle. Printed in the UK. 3M, Scotchgard and Solus are trademarks of 3M Company. © 3M 2022. All rights reserved. OMG315066

This version is the sole document applicable to the product(s) since its date of publication.

