

# 3M™ Virtua™ AP Series Safety Glasses

## Technical datasheet



### Product description

The 3M™ Virtua™ AP Series Safety Glasses has a wrap around design and features an integral side shield for improved safety and greater protection. The design offers excellent coverage and field of vision. These products are available in either clear or grey lenses. The grey lenses help protect against sun glare.

### Product range

Product ID	Description	Lens colour	Frame colour
Virtua AP Clear	3M™ Virtua™ AP Safety Glasses with clear PC lens	Clear PC	Clear
Virtua AP Grey	3M™ Virtua™ AP Safety Glasses with grey PC lens	Grey PC	Grey

### Typical applications

These products can be used in a wide range of applications including:

- ▶ Industrial manufacturing
- ▶ Construction
- ▶ Engineering
- ▶ General assembly
- ▶ Woodworking
- ▶ Light duty maintenance and repair

### Intended use

These products are intended for protection against high speed particles at low energy (F) at extreme temperature conditions, -5°C and +55°C, (T) in accordance with EN 166:2001.

These products also help protect against UV radiation in accordance with EN 170:2002 (clear and amber lenses), and sun glare in accordance with EN 172:1994 (grey).

A number of lens options are available for a variety of different applications:

- ▶ Clear – Good colour recognition and excellent UV protection
- ▶ Grey – Good for protection from sun glare

### Key features

- ▶ Wrap-around design provides excellent coverage and good field of vision
- ▶ Optical Class 1 to allow prolonged comfortable wear
- ▶ Unisex design
- ▶ Offers excellent protection against UV radiation
- ▶ Integrated brow bar for added protection
- ▶ Lens coatings provide scratch resistance
- ▶ Lightweight (26g) for maximum comfort

### Use limitation

- ▶ Never modify or alter this product
- ▶ Do not use this product against hazards other than those specified in this document
- ▶ In accordance with EN 166:2001 safety spectacles cannot be tested and approved for use against liquid droplets. Where liquid protection is specified a suitable product should be considered, for example safety goggles
- ▶ These products are not suitable for grinding or welding
- ▶ These products are NOT designed to be worn over prescription spectacles

### Standards and approval

These products are type examined by BSI Group, Notified Body number 2797.

These products are CE marked to the requirements of European Regulation (EU) 2016/425.

[GB only]: These products are type examined by BSI Assurance UK Ltd, Kitemark Court, Davy Avenue, Knowlhill, Milton Keynes MK5 8PP, UK, Approved Body No. 0086.

These products are UKCA marked and meet the requirements of Regulation 2016/425 on personal protective equipment, as amended to apply in GB.

The applicable legislation can be determined by reviewing the Certificates and Declarations of Conformity at [www.3M.com/Eye/certs](http://www.3M.com/Eye/certs)

## Materials listing

Description	Material
Lens	Polycarbonate
Temple arms	Polycarbonate
Screws	Stainless steel

## Marking

The products have demonstrated compliance with the requirements of EN 166:2001 and associated standards and bear the following marks:

Product ref	Lens marking	Frame marking
Virtua AP Clear	2C-1.2 3M 1 FT	3M EN 166 FT CE
Virtua AP Grey	5-2.5 3M 1 FT	3M EN 166 FT CE

## Explanation of marking

Marking	Description
2C-1.2 (EN 170:2002)	UV protection This product conforms to the requirements of the standard, providing UV protection for the complete specified range (210nm – 365nm). Products marked C provide good colour recognition
5-2.5 (EN 172:1994 as amended)	Sun-glare protection conforming to the requirements of the standard, providing UV protection for the complete specified range (280nm – 350nm)
1	Optical class
F	Impact protection against high speed particle at low energy (45m/s)
T	Tested for impact protection at extreme temperature conditions -5°C and +55°C

## IMPORTANT NOTICE

The use of the 3M product described within this document assumes that the user has previous experience of this type of product and that it will be used by a competent professional. Before any use of this product it is recommended to complete some trials to validate the performance of the product within its expected application.

All information and specification details contained within this document are inherent to this specific 3M product and would not be applied to other products or environment. Any action or usage of this product made in violation of this document is at the risk of the user.

Compliance to the information and specification relative to the 3M product contained within this document does not exempt the user from compliance with additional guidelines (safety rules, procedures). Compliance to operational requirements especially in respect to the environment and usage of tools with this product must be observed. The 3M group (which cannot verify or control those elements) would not be held responsible for the consequences of any violation of these rules which remain external to its decision and control.

Warranty conditions for 3M products are determined with the sales contract documents and with the mandatory and applicable clause, excluding any other warranty or compensation.

For more information on 3M products and services please contact 3M.

### Personal Safety Division

3M United Kingdom PLC  
3M Centre, Cain Road  
Bracknell, Berkshire RG12 8HT  
Tel.: 0870 60 800 60  
[www.3M.eu/Safety](http://www.3M.eu/Safety)

3M Ireland Limited  
The Iveagh Building  
Carrickmines Park,  
Carrickmines  
D18 X015 Ireland  
+353 (0)1 280 3555

Please recycle. Printed in the UK. © 3M 2022. 3M and Virtua are trademarks of 3M Company. All rights reserved. OMG315066.

