

# Anybus Communicator - PROFINET IO-Device - Modbus TCP server

The Anybus Communicator PROFINET IO-Device – Modbus TCP server is an industrial protocol gateway that allows you to seamlessly transfer data between PLC control systems over PROFINET and Modbus TCP networks.

Anybus Communicators are designed to ensure reliable, secure, and high-speed data transfer between different industrial Ethernet and Fieldbus networks. Very easy to install and deploy, the stand-alone gateways enable transparent data exchange between PLCs allowing you to both bridge and integrate legacy equipment into modern high-performance networks with only minimal changes to the software.

Anybus Communicators are built using the award-winning and proven Anybus NP40 industrial network processor providing network conformance, high performance, and reliability. When connecting between PLCs on different networks, extremely fast data cycling is enabled with data transfer of up to 1500 bytes in each direction, meeting most current control application needs as well as supporting future demands.

Quick installation is ensured thanks to the intuitive configuration, easy-to-understand documentation, and smart hardware and housing design.



# **Excellent performance**

- Instant data transfer The time it takes to transfer data between two PLCs consists of the cycle time on the first network plus the cycle time on the second network. Internal data transfer in the Communicators is negligible as it's in line with the natural variation of the network cycle times (jitter).
- Hardware-accelerated endian conversion (byte swap) The Communicators can change the data representation (endianness) through a
  hardware-accelerated endian conversion to ensure data is presented correctly in each PLC. You can even convert different parts of the
  data area in different ways to handle different data types. It has no impact on performance, offloads the PLC of the data conversion
  task, and simplifies PLC programming.

#### Easy to Use

- Dedicated ethernet configuration port no special cables required.
- Intuitive web-based drag and drop configuration interface no need to install any additional software.
- · Forward-facing ports make it easy to connect cables and the slim form factor saves space on the DIN rail.
- Troubleshoot problems with powerful diagnostics including live data monitor, status screen, and support package.

# **Latest Security Features**

Secure boot functionality to detect tampering with firmware and resist attacks and infection from malware. ecurity switch which locks your configuration and prevents any unauthorized access.

## **Designed for industrial environments**

- Robust compact housing.
- Industrial components are tested and certified according to CE and UL.
- Wide temperate range, -25°C to 70°C.
- DIN-rail mounting to enable installation close to connected devices, reducing the amount of wiring.



### **PROFINET FEATURES**

- PROFINET IO-Device (slave)
- Transfer up to 1 024 bytes to and from PROFINET (2048 bytes total)
- 1 ms minimum cycle time
- Conformance class B, Real-Time (RT)
- High robustness against network load, Netload Class III
- Dual RJ45 Ethernet ports with 10/100 Mbit full duplex
- Daisy chaining with integrated switch

### **MODBUS TCP FEATURES**

- Modbus TCP server
- Transfer up to 1 500 bytes to and from Modbus TCP (3 000 bytes total)
- 4 connections
- Function codes 01-06, 15-16, 23, 43/14
- Dual RJ45 Ethernet ports with 10/100 Mbit full duplex
- Daisy chaining with integrated switch

### **GENERAL**

Dimensions (L x W x H) with serial and power connector	98 x 27 x 144 mm 3.85 x 1.06 x 5,67 in
Weight	150 grams, 0.33 lb
Buttons and switches	Reset button and security switch
LEDs	Gateway, Network 1 & Network 2
IP rating	IP20
Housing material	PC ABS, UL 94 VO
Mounting	DIN rail (35 * 7,5/15)

#### **ENVIRONMENT**

perating temperature	-25 to 70° C, -13 to 158° F

Storage temperature	-40 to 85° C, -40 to 185° F
Relative humidity	0-95% non condensing
Installation altitude	Up to 2 000 m

## **POWER**

Input voltage	12 - 30 VDC
Current consumption	Typical: 160 mA @ 24V Max: 400 mA @ 12V
Power connector	3-pin plug with screw terminal
Protection	Reverse voltage protection and short circuit protection

## **ETHERNET PORTS**

Ports	2+2 x Ethernet
Isolation	Galvanic isolation
Bitrate	10/100 Mbit full duplex
Connector	RJ45
Switch.	Dual port cut-through switch

## PROFINET

Mode	PROFINET IO-Device (slave)
Class	А, В
Communication channels	Real Time Channel (RT)
Input data size	1 024 bytes
Output data size	1 024 bytes
Minimum cycle time	1 ms
Max number of connections	1 IO Controller Application Relationship + 2 Device Access Application Relationships
Netload class	Class III
I&M records	Manufacturer data (I&M0), Tag information (I&M1), Date/Time (I&M2), Description (I&M3)
SNMP	Available
GSDML File	Available
Certification	Pending

# **MODBUS TCP**

	lode	Server
1		

Max number of connections	4
Input data size	1 500 bytes
Output data size	1 500 bytes

# **CERTIFICATIONS AND STANDARDS**

UL	CUL <sub>US</sub> file number E214107
CE	2014/30/EU
кс	R-R-ABJ-Communicator
ЕМС	EN 61000-6-2 EN 61000-4-2 EN 61000-4-3 EN 61000-4-4 EN 61000-4-5 EN 61000-4-6 EN 61000-6-4 EN 55032
Environment	IEC 60068-2-1 Ab IEC 60068-2-2 Bb IEC 60068-2-1 Ab IEC 60068-2-2 Bb IEC 60068-2-14 Nb IEC 60068-2-30 Db IEC 60068-2-78 Cab IEC 60068-2-78 Cab
Vibration and shock	IEC 60068-2-27 IEC 60068-2-6
Waste certification	WEE

# CONFIGURATION

Configuration software	Web based configuration
Configuration ports	Dedicated 10/100 Mbit RJ45 Ethernet configuration port and Ethernet ports

# **SECURITY**

Secure boot	Ensures software authenticity
Security switch	Physical switch that enable/disable access to the web based configuration interface

# PRODUCT PACKAGING

Content	Gateway, power connector, start-up guide, compliance information sheet
Sox material	Cardboard

### **MEAN TIME BETWEEN FAILURE**

MTBF	> 1500000 h, Telcordia Method I Case 3 at 30° C

# Ordering Information

ORDER CODE: ABC4017 WARRANTY: 3 years

For purchasing instructions and terms and conditions, see: <u>How to buy</u>

Copyright © 2020 HMS Industrial Networks - All rights reserved.

