



Passive Components > Resistors > Chassis Mount Resistors > Power Resistor: Aluminum Housed, 75 Watt



Resistor Type: **Power Resistor**

Passive Component Dimensions: **36.5 x 21 x 11 mm**

Number of Terminations: **2**

Packaging Method: **Loose Piece - Tray**

Passive Component Tolerance: **5 %**

[All Power Resistor: Aluminum Housed, 75 Watt \(236\)](#)

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Wire Wound

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Voltage Rating	265 VDC
Passive Component Tolerance	5 %
Resistance Class	Up to 1kΩ
Resistance Value	3.3 Ω
Power Rating	15 W

Termination Features

Number of Terminations	2
Chassis Mount Resistor Termination Type	Solder Lug

Mechanical Attachment

Chassis Mount Resistor Mount Style	Chassis Mount
------------------------------------	---------------

Dimensions

--



Passive Component Dimensions	36.5 x 21 x 11 mm
------------------------------	-------------------

Usage Conditions

Temperature Coefficient	±50 ppm/°C
-------------------------	------------

Packaging Features

Packaging Method	Loose Piece - Tray
------------------	--------------------

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Hand solderable with lead free solder

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-C339-T419
Power Resistor: Aluminum Housed, 75 Watt



Also in the Series | CGS THS



Chassis Mount Resistors(237)



PCI & PCI Express Connectors(8)

Customers Also Bought




TE Part #1367645-6
DWDM Kit Assy, Networking (13)



TE Part #1-1879138-2
RN 0603 2K05 0.1% 10PPM 5K RL



TE Part #9-1879334-7
CPF 0603 20R 1% 50PPM 1K RL



TE Part #1963850-2
XFP. MSA HEATSINK 10mm TALL




TE Part #2842142-5
10P,2MM,BRK HDR,DRV,VT,SMD,0.1AU, TR W/CAP




TE Part #4-2176345-6
CRGCQ 1210 56K 1%



TE Part #1-2176308-7
RP 1E 0.1W 196K 0.1% 25PPM 5K RL



TE Part #1734598-5
1.25 WTB HDR DIP, 5 POS



TE Part #280613-2
10P MOD 1 SHROUDED HEADER, ST, 0.4 Au



TE Part #7-2176280-4
CPF 0402 301K 0.1% 25ppm 5K RL

Documents

Product Drawings

THS15 3R3 5%

English

CAD Files

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_1-1879074-1_BB.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1879074-1_BB.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1879074-1_BB.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[4-1773460-6_RESISTIVE_SOLUTIONS_RAIL](#)

English

[1309350_PASSIVE_COMPONENT](#)

English

[Aluminium Housed Power Resistors - Type THS Series - Tyco Electronics Passives](#)

English

[8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS](#)

English