



Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **Power Resistor**

Passive Component Dimensions: **19 x 7 mm**

Number of Terminations: **2**

Packaging Method: **Loose Piece - Box**

Passive Component Tolerance: **10 %**

Features

Product Type Features

Product Type	Fixed Resistor
Resistor Type	Power Resistor
Element Type	Ceramic Composition

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Voltage Rating	400 V
Passive Component Tolerance	10 %
Resistance Class	1kΩ – 1MΩ
Resistance Value	1K Ω
Power Rating	2 W

Body Features

Passive Component Lead Type	Axial-Leaded
-----------------------------	--------------

Termination Features

Number of Terminations	2
Passive Component Termination Material Type	Tinned Copper Leads

Dimensions

Passive Component Dimensions	19 x 7 mm
------------------------------	-----------



Usage Conditions

Operating Temperature Range	-40 – 200 °C
Temperature Coefficient	±1300 ppm/°C

Packaging Features

Packaging Method	Loose Piece - Box
------------------	-------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

CCR21K0KB

Through-Hole Resistors, Power Resistor, 19 x 7 mm, 2 Termination, Loose Piece - Box,
10 %, Ceramic Composition, Resistance Class 1kΩ – 1MΩ, CGS CCR



TE Part # 1-1623719-4
CCR1 10K 10%



TE Part # 1623719-8
CCR1 10R 10%



TE Part # 1-1623719-2
CCR1 470R 10%



TE Part # 1-1623719-0
CCR1 47R 10%



TE Part # 1-1623719-3
CCR1 4K7 10%



TE Part # 2-1623720-8
CCR2 56R 10%



TE Part # 1-1623720-8
CCR2 68R 10% BULK



TE Part # 3-1623720-1
CCR2 120K 10%



TE Part # 1623720-3
CCR2 10R 10%



TE Part # 1623719-5
CCR1 100R 10%



TE Part # 1623719-9
CCR1 15R 10%



TE Part # 1623719-4
CCR1 22R 10%



TE Part # 1623720-1
CCR2 100R 10%



TE Part # 1623720-2
CCR2 10K 10%



TE Part # 2-1623720-9
CCR2 15K 10%



TE Part # 1623720-5
CCR2 220R 10%



TE Part # 1623720-6
CCR2 22K 10%



TE Part # 2-1623720-6
CCR2 27R 10%



TE Part # 1-1623720-3
CCR2 33R 10%



TE Part # 1623720-8
CCR2 470R 10%

Also in the Series | CGS CCR



Through-Hole Resistors(62)

Customers Also Bought



TE Part #1612618-4
SEMI-HARD TRAY DDR2 SODIMM
SOCKET 200P 9



TE Part #4-2176055-4
RLP73K 2B R62 1% 1K RL



TE Part #1-1470108-0
2.0MM PITCH HEADER,DIP 10P



TE Part #5-1614352-2
RN 0603 2K15 0.1% 10PPM CUT
LENGTH



TE Part #1623708-1
RGP0207CH 5% 100M




TE Part #6651457-1
CONN,PIN HOUSING



TE Part #3-1625885-6
1W SM M/OX 5% 1M0



TE Part #6-1393227-5
RTE24006F



TE Part #5-2176345-5
CRGCQ 1210 330K 1%



TE Part #2-2176372-0
RQ 0603 78K7 0.1% 10PPM 5K RL

Documents

Product Drawings

CCR2 1K0 10%

English

CAD Files

Customer View Model

ENG_CVM_CVM_1623720-4_BA.2d_dxf.zip

English

3D PDF



3D

Customer View Model

[ENG_CVM_CVM_1623720-4_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1623720-4_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[4-1773460-6_RESISTIVE_SOLUTIONS_RAIL](#)

English

[1309350_PASSIVE_COMPONENT](#)

English

[Ceramic Composition Resistors - Type CCR Series - Tyco Electronics Passives](#)

English

[8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS](#)

English