LR0204F2K4 ✔ ACTIVE

Neohm | Neohm LR

TE Internal #: 1622210-1

Through-Hole Resistors, General Purpose Resistor, 3.5 x 2 mm, 2 Termination, 0204, Ammo Packed, 1 %, Thin Film, Resistance Class 1kΩ – 1MΩ, Neohm LR

View on TE.com >

Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **General Purpose Resistor**

Passive Component Dimensions: **3.5 x 2 mm**

Number of Terminations: **2**

Package Size Code: **0204**

Packaging Method: **Ammo Packed**

Features

Product Type Features

Product Type	Fixed Resistor
Resistor Type	General Purpose Resistor
Package Size Code	0204
Element Type	Thin Film

Configuration Features

Number of Resistors	1

Electrical Characteristics

Voltage Rating	200 V
Passive Component Tolerance	1 %
Resistance Class	1kΩ – 1MΩ
Resistance Value	2.4K Ω
Power Rating	.25 W

Body Features

Passive Component Lead Type	Axial-Leaded

Termination Features

Number of Terminations	2
Passive Component Termination Material Type	Tinned Copper Leads

Dimensions

Passive Component Dimensions	3.5 x 2 mm

Usage Conditions

Operating Temperature Range	-55 – 155 °C
Temperature Coefficient	±100 ppm/°C

Packaging Features

Packaging Method	Ammo Packed

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 1622367-1
LR1 1% 1M0



TE Part # 1622298-1
LR1 1% 10K



TE Part # 1622598-1
LR1L 5% R10



TE Part # 1614978-1
LR0204 1% 10K



TE Part # 1622742-1
LR2 1% 39K

Also in the Series | Neohm LR



DIMM Sockets(5)



Through-Hole Resistors(492)

Customers Also Bought



TE Part #8-188275-8
MICRO-MATCH SMD FTE



TE Part #177916-1
AMP POWER DBL LOCK TAB (S)




TE Part #2176232-4
3522 180K 1% 3W



TE Part #350690-3
UMNL PIN 24-18 PTPPHBZ L/P



TE Part #66103-2
III+ PIN,24-20,TIN-LEAD,LP



TE Part #350689-3
UMNL SOK 24-18 PTPPHBZ L/P




TE Part #66099-2
III+ PIN,18-16,TIN-LEAD,LP



TE Part #8-215460-0
MICRO-MATCH FSID P



TE Part #6-1768034-2
LKZ12B4



TE Part #1487588-1
USB, A-B, 28/24, WHITE, 2.0M

Documents

Product Drawings

LR0204 1% 2K4

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1622210-1_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1622210-1_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1622210-1_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

Metal Film Fixed Resistors - Type LR Series - Tyco Electronics Passives

English