

LR1F16R

✓ ACTIVE

Neohm | Neohm LR

TE Internal #: 1622334-1

Through-Hole Resistors, General Purpose Resistor, 6.2 x 2.3 mm, 2 Termination, Ammo Packed, 1 %, Thin Film, Resistance Class Up to 1kΩ, 16 Ω, Neohm LR

[View on TE.com >](#)



Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **General Purpose Resistor**
Passive Component Dimensions: **6.2 x 2.3 mm**
Number of Terminations: **2**
Packaging Method: **Ammo Packed**
Passive Component Tolerance: **1 %**

Features

Product Type Features

Product Type	Fixed Resistor
Resistor Type	General Purpose Resistor
Element Type	Thin Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Voltage Rating	350 V
Passive Component Tolerance	1 %
Resistance Class	Up to 1kΩ
Resistance Value	16 Ω
Power Rating	.6 W

Body Features

Passive Component Lead Type	Axial-Leaded
-----------------------------	--------------

Termination Features

Number of Terminations	2
Passive Component Termination Material Type	Tinned Copper Leads

Dimensions

Passive Component Dimensions	6.2 x 2.3 mm
------------------------------	--------------



Usage Conditions

Operating Temperature Range	-55 – 155 °C
Temperature Coefficient	±50 ppm/°C

Packaging Features

Packaging Method	Ammo Packed
------------------	-------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1622367-1
LR1 1% 1M0

TE Part # 1622298-1
LR1 1% 10K

TE Part # 1622598-1
LR1L 5% R10

TE Part # 1614978-1
LR0204 1% 10K

TE Part # 1622742-1
LR2 1% 39K

Also in the Series | Neohm LR

DIMM Sockets(5)

Through-Hole Resistors(492)

Customers Also Bought

TE Part #1415015-1
SR6A4024 - V23050-A1024-A533

TE Part #3-2176057-3
RLP73K 3A R22 1% 1K RL

TE Part #1-826631-0
AMPMODU II R/A DR HEADER

TE Part #1-2176089-0
RP 1J 0.166W 13K3 0.1% 25PPM 1K RL

TE Part #2176331-9
CRGP 2512 47R 1%

TE Part #4-2176371-3
RQ 0603 12K7 0.1% 10PPM 5K RL

TE Part #9-2176370-6
RQ 0603 4K22 0.1% 10PPM 5K RL

TE Part #87224-1
01 MODII HDR SRST UNSHRD .100



Documents

Product Drawings

LR1 1% 16R

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1622334-1_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1622334-1_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1622334-1_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

Metal Film Fixed Resistors - Type LR Series - Tyco Electronics Passives

English