



Application Tooling > Applicators



Applicator Feed Type: **Pneumatic**

Applicator & Product Style: **OCEAN**

Application Interface: **Male Adapter Post - Atlantic Style**

Terminator Type: **30 mm (1.12") Stroke Terminator, 40 mm (1.62") Stroke Terminator**

Service Options: **Capability Study, Crimped Samples, Cross Section - Photograph**

Features

Other

Applicator Feed Type	Pneumatic
Applicator & Product Style	OCEAN
Application Interface	Male Adapter Post - Atlantic Style
Terminator Type	30 mm (1.12") Stroke Terminator, 40 mm (1.62") Stroke Terminator
Service Options	Capability Study, Crimped Samples, Cross Section - Photograph
Alignment Aids	Alignment Gauge, Camera

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC
Free


Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2217000-1 G II CE TERMINATOR	 TE Part # 2161500-1 AMP 5K/40 CE TERMINATOR	 TE Part # 2-2119582-4 Crimper, Insulation F Premium	 TE Part # 690474-6 SHEAR BLADE
 TE Part # 1-1803000-5 ANVIL, COMBINATION, END FEED	 TE Part # 2161400-5 AMP 3K/40 CE EL TERMINATOR	 TE Part # 2161500-2 AMP 5K/40 CE TERMINATOR, W/CQM	 TE Part # 2161700-4 5K CE STRIPPING MODULE
 TE Part # 2161700-5 5K CE STRIPPING MODULE W/ CQM	 TE Part # 2217000-2 MODEL G II CE TERMINATOR, W /CQM	 TE Part # 2217001-3 MODEL G II STRIPPING MODULE	 TE Part # 2217001-4 MODEL G II STRIPPING MODULE W /CQM



TE Part # 2362229-1
DCC TERMINATOR, 5K ATLANTIC

TE Part # 2362229-3
DCC TERMINATOR, GII ATLANTIC

TE Part # 3-2161500-1
AMP 5K/30 CE TERMINATOR

TE Part # 3-2161500-2
AMP 5K/30 CE TERMINATOR, W/COM

TE Part # 4-2161500-0
AMP 5K/40 CE TERM OVERSIZED
GUARD, AF

TE Part # 5-456403-0
CRIMPER, WIRE .062F

TE Part # 7-2150246-7
OC-062F140F-CRIMPTOOLINGKIT

TE Part # 160778-2
187 FASTON, REC., 24-20 AWG, TPBR

Customers Also Bought

TE Part #2-683452-9
ANVIL

TE Part #567408-2
HDMHB 9EAPR160T180O G

TE Part #6-1424909-6
CRIMPER, INSULATION "F"(.240")

TE Part #6-456134-7
CRIMPER, INSULATION "F"(.210")

TE Part #680588-3
HDM 9HBAPR140S140OG

TE Part #852293-3
MACH,U-POD.250 9SAPR11OF18OF G

TE Part #CX2740-000
ES2000-NO.3-B8-0-130MM

TE Part #121397P013
ES2000-NO.3-B8-0-41MM

TE Part #CZ8200-000
VERSAFIT-3/4-0-2.25IN

Documents



Product Drawings

OC-AT-E-FA-070F130F-001-0046

English

Datasheets & Catalog Pages

TE_APPLICATORS_CATALOG

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English