2234074-1 ✔ ACTIVE

AMP

TE Internal #: 2234074-1

Applicators, Mechanical Feed, OCEAN, Male Adapter Post - Atlantic Style Interface, 30 mm (1.12") Stroke Terminator / 40 mm (1.62") Stroke Terminator

View on TE.com >

Application Tooling > Applicators



Applicator Feed Type: **Mechanical**

Applicator & Product Style: **OCEAN**

Application Interface: **Male Adapter Post - Atlantic Style**

Terminator Type: **30 mm (1.12") Stroke Terminator, 40 mm (1.62") Stroke Terminator**

Wire Crimp Width: **2.85 mm [.112 in]**

Features

Termination Features

Wire Crimp Form	F

Dimensions

Wire Crimp Width	2.85 mm[.112 in]

Other

Applicator Feed Type	Mechanical
Applicator & Product Style	OCEAN
Application Interface	Male Adapter Post - Atlantic Style
Terminator Type	30 mm (1.12") Stroke Terminator, 40 mm (1.62") Stroke Terminator
Service Options	Capability Study, Crimped Samples, Cross Section - Photograph
Alignment Aids	Alignment Gauge, Camera

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 1803095-6
FLOATING SHEAR, FRONT



TE Part # 2119805-1
SHEAR HOLDER, FRONT, CUT



TE Part # 2119806-1
INSERT, SHEAR



TE Part # 2362229-1
DCC TERMINATOR, 5K ATLANTIC



TE Part # 2362229-3
DCC TERMINATOR, GII ATLANTIC




TE Part # 3-2161500-2
AMP 5K/30 CE TERMINATOR, W/CQM



TE Part # 5-1633609-2
CRIMPER, WIRE F



TE Part # 6-1803514-3
ANVIL, COMBINATION



TE Part # 7-2234074-7

OCEAN_2.0_SPARE_PART_KIT-112F152OV



TE Part # 9-1633963-7


CRIMPER, INSULATION OVERLAP

Customers Also Bought



TE Part #DT04-2P

DEUTSCH DT Series Housings & Connectors



TE Part #W2S

DEUTSCH DT WEDGELOCKS




TE Part #282104-1

AMP SUPERSEAL 1.5MM, CONNECTOR HOUSING



TE Part #206070-8

CABLE CLAMP KIT #17



TE Part #281934-2

SINGLE WIRE SEAL



TE Part #0460-202-16141

DEUTSCH SOLID CONTACTS

Documents

Datasheets & Catalog Pages

1-1773864-9_1015_TE_APPLICATORS-US 2015

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English