



Application Tooling > Spare & Wear Tooling



Applicator & Product Style: **Standard**

Features

Other

|                            |          |
|----------------------------|----------|
| Applicator & Product Style | Standard |
|----------------------------|----------|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                       |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2022 (224)<br>Candidate List Declared Against: JUNE 2022 (224)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                             |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                    |

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

|                                                                                                                                          |                                                                                                                                         |                                                                                                                                           |                                                                                                                                          |
|------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------|
|  <p>TE Part # 680881-1<br/>HINGE BAR 9EAPR140 TL TG</p> |  <p>TE Part # 680881-2<br/>HINGE BAR 9EAPR140TL K</p> |  <p>TE Part # 680882-1<br/>HINGE BAR 9EAPR140TL TG</p> |  <p>TE Part # 680882-2<br/>HINGE BAR 9EAPR140TL K</p> |
|------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------|

Customers Also Bought

|                                                                                                                                          |                                                                                                                                                        |                                                                                                                                              |                                                                                                                                     |
|------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------|
|  <p>TE Part #4160-203-1631L<br/>CONT PIN</p>           |  <p>TE Part #60960-3<br/>250 FASTON FLAG REC 12-10 AWG<br/>TPBR</p> |  <p>TE Part #350538-1<br/>UMNL PIN 20-14 .0126 PTPBR</p> |  <p>TE Part #455838-2<br/>ANVIL INSERT</p>      |
|  <p>TE Part #691531-5<br/>WIRE CRIMPER-REVERSIBLE</p> |  <p>TE Part #691532-6<br/>SHEAR BLADE</p>                          |  <p>TE Part #2-24607-7<br/>SCREW,CAP,SOC FLAT HD</p>    |  <p>TE Part #691525-6<br/>PLATE REAR SHEAR</p> |
|  <p>TE Part #692655-1<br/>AIR FEED VALVE ASSY</p>     |  <p>TE Part #694427-1<br/>BRACKET HOLD DOWN</p>                    |                                                                                                                                              |                                                                                                                                     |

Documents

Datasheets & Catalog Pages

CRIMPING WHERE FORM MEETS FUNCTION

English

Instruction Sheets

Instruction Sheet (U.S.)

English

