



Application Tooling > Spare & Wear Tooling



Applicator & Product Style: OCEAN

Features

Other

| | |
|----------------------------|-------|
| Applicator & Product Style | OCEAN |
|----------------------------|-------|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|--|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Out of Scope |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-2151301-2
OCEAN-2.0-APPLICATOR-S-070F090F



TE Part # 2151301-2
OCEAN-2.0-APPLICATOR-S-070F090F



KIT
REPRESENTATION ONLY

TE Part # 7-2151301-7
OCEAN_2.0_SPARE_PART_KIT-070F090F

Customers Also Bought



TE Part #1633965-1
CRIMPER, INSUL O PREMIUM



TE Part #1333231-4
ANVIL, COMBINATION SPECIAL



ANVIL
REPRESENTATION ONLY

TE Part #1333231-9
ANVIL, COMBINATION, SPECIAL



TE Part #1333232-5
ANVIL, COMBINATION,SPECIAL



TE Part #3-1633738-2
CRIMPER, WIRE F .040



CRIMPER
REPRESENTATION ONLY

TE Part #3-1633966-4
CRIMPER,INSULATION O



TE Part #5-568176-0
CRIMPER,WIRE

TE Part #879103-2
EINSTELLK. F ASSY

TE Part #2389761-7
RBK-ILS-PROC-EJECT-BL-SET

TE Part #562669-1
ANSCHLAG

Documents

Datasheets & Catalog Pages

[CRIMPING WHERE FORM MEETS FUNCTION](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

