



Connectors > Automotive Connectors > Automotive Housings



Connector & Housing Type: **Housing for Female Terminals**

Mating Tab Width: **2.8 mm [.11 in]**

Connector System: **Wire-to-Board, Wire-to-Device, Wire-to-Wire**

Number of Positions: **2**

Centerline (Pitch): **10.4 mm [.409 in]**

Features

Product Type Features

Connector Shape	Rectangular
Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Board, Wire-to-Device, Wire-to-Wire
Sealable	Yes
Hybrid Connector	No
Primary Locking Feature	On the Terminal

Configuration Features

Number of Positions	2
---------------------	---

Electrical Characteristics

Operating Voltage	750 VDC
Nominal Voltage Architecture	12 V, 24 V, 42 V, 48 V, 80 V, 90 V, 125 V, 240 V, 500 V, 550 V, 600 V

Body Features

Cable Exit Angle	180°
Primary Product Color	Black

Contact Features

Contact Size	2.8mm
--------------	-------



Contact Type	Receptacle
Mating Tab Width	2.8 mm[.11 in]

Mechanical Attachment

Terminal Position Assurance	No
Strain Relief	With
Mating Alignment Type	Polarized
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PA GF
Centerline (Pitch)	10.4 mm[.409 in]

Dimensions

Connector Height	42.45 mm[1.671 in]
Product Width	42.45 mm[1.671 in]
Product Length	19.3 mm[.76 in]

Usage Conditions

Operating Temperature (Max)	70 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C, 140 °C[158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F][284 °F]
Operating Temperature Range	-40 – 140 °C[-40 – 284 °F]

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Degree of Protection	IP6K9K
UL Flammability Rating	UL 94HB

Other

Serviceable	No
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2103169-2
OUTER HOUSING, CAP, KEY B,
HVA280-2PHM



TE Part # 2103169-1
OUTER HOUSING, CAP, KEY A,
HVA280-2PHM



TE Part # 2103169-4
OUTER HOUSING, CAP, KEY D,
HVA280-2PHM



TE Part # 2103169-5
OUTER HOUSING, CAP, KEY E,
HVA280-2PHM



TE Part # 2103169-6
OUTER HOUSING, CAP, KEY F,
HVA280-2PHM

Also in the Series | **HVA 280**



Automotive Connector Caps & Covers (4)	Automotive Connector EMC Shielding (15)	Automotive Housings(74)	Automotive Seals & Cavity Plugs(8)
Electric, Hybrid & Fuel Cell Cable Assemblies(6)	High Voltage Wire Processing Equipment(7)	Other Automotive Connector Accessories(37)	PCB Headers & Receptacles(37)

Customers Also Bought

TE Part #329656 SPLICE,TERMI-FOIL DBL FACE	TE Part #3-2176363-8 RQ 0402 1K05 0.1% 10PPM 5K RL	TE Part #5677772002 RNF-3000-3/1-6-STK	TE Part #892979-000 22759/32-14-0
TE Part #2103155-3 COLLET, SIZE 3, HVA280	TE Part #2103169-5 OUTER HOUSING, CAP, KEY E, HVA280-2PHM	TE Part #7-1618413-2 K1K06H024EAHA= CONTACTOR SPST-NO W/AUX	TE Part #7-2176422-8 TLRP 2512 3.0W R150 1% 50PPM 4K RL
TE Part #6-160316-4 110 FASTON REC 22-20 AWG TPBR	TE Part #2103154-3 CABLE SEAL, SIZE 3, HVA280		

Documents



Product Drawings

INNER HOUSING, CAP, HVA280-2PHM

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2103170-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2103170-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2103170-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

HEMS Product Overview

English