49975 ✔ ACTIVE

AMP

TE Internal #: 49975

Hand Crimping Tools, Premium Crimp Tooling, Not Releasable, Not Adjustable, Fixed In Tool, TE Product Specification (108-), Manual / Battery

View on TE.com >

Application Tooling > Hand Crimping Tools



Tool Grade: **Premium Crimp Tooling**

Ratchet Configuration: **Not Releasable, Not Adjustable**

Die Sets Type: **Fixed In Tool**

Specification Type: **TE Product Specification (108-)**

TE Certification: **Yes – Certificate Included**

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - W Crimp
Tool Grade	Premium Crimp Tooling
Ratchet Configuration	Not Releasable, Not Adjustable
Die Sets Type	Fixed In Tool
Specification Type	TE Product Specification (108-)
TE Certification	Yes – Certificate Included
Power Technology Type	Battery, Manual
Tooling Type	Double Action Hand Tool

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC

Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 31181
TERMINAL,BODY FLAG R 16-14 10



TE Part # 325069
TERMINAL,SOLIS FLAG R 16-14 8



TE Part # 322819
TERMINAL,SOLIS FLAG R 16-14 10



TE Part # 53264-2
TERMINAL,TERMI-FOIL 14-12

Customers Also Bought




TE Part #5747846-3
25 MSFL RCPT RA 318 (IN,FM,BL)



TE Part #747847-4
37 MSFL RCPT RA 318 (IN,FM,BL)



TE Part #5747845-4
D-Sub Receptacle Assembly: Right Angle, Shell Size 2, 2.74mm



TE Part #5747844-4
09 MSFL RCPT RA 318 (IN,FM,BL)



TE Part #166916-000
RMW-63/19-1200/ADH-0



TE Part #YDTS20W09-35BAV001
RECP ASSY



TE Part #YDTS24W09-35SAV001
RECP ASSY



TE Part #179544-000
D-181-2222-90/9



TE Part #YDTS33T11NV0010000
CAP ASSEMBLY

Documents

Product Drawings

DAHT TERMI-FOIL 18-12 ASSY

English

Datasheets & Catalog Pages

Bottoming Dies

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Hand Crimping Tools 49769, 49965, and 49975

English