



Application Tooling > Spare & Wear Tooling



Applicator & Product Style: **Tab-lok**

Features

Other

Applicator & Product Style	Tab-lok
----------------------------	---------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 1855041-1 HINDGE BAR F.A. EMPO160TAB180O LM & G	 TE Part # 1855468-1 HDM/FA/HB EMPO160TABLOCK180O LM & G	 TE Part # 1855521-1 HDM/FA/HB EMPO200TL220O LM CUT	 TE Part # 567303-1 APPL,HINGE BAR 9EMPO160T180O T
 TE Part # 687388-6 MHB 9EAPR200T220O G	 TE Part # 687389-4 M HBEAPR200T220OK	 TE Part # 687389-6 HDM HB 9EMPR200T220O G	 TE Part # 687395-8 HINGE BAR 9EAPR160T180O G
 TE Part # 687395-9 EF HINGE BAR 9EMPR160TL210O T	 TE Part # 687388-1 M HBEMPO200T220OT	 TE Part # 687388-5 M HBEAPR200T220OK	 TE Part # 687389-1 M HBEMPO200T220OT
 TE Part # 687395-1 END FEED HINGE BAR APPLICATOR			

Customers Also Bought

 TE Part #42660-2 250 FASTON REC 18-14 AWG TPBR	 TE Part #690587-1 WIRE CRIMPER	 TE Part #690575-1 ANVIL-REVERSIBLE	 TE Part #454568-1 FEED FINGER
---	---	---	--





TE Part #690569-1
FRONT SHEAR PLATE



TE Part #454711-1
PLATE, REAR SHEAR



TE Part #354004-8
INSERT, ANVIL



TE Part #354004-5
INSERT, ANVIL



TE Part #692134-1
POSITIONER, TERM. (.125) 41531



TE Part #692134-1
POSITIONER, TERM. (.125) 41531

Documents

Datasheets & Catalog Pages

CRIMPING WHERE FORM MEETS FUNCTION

English

Instruction Sheets

Instruction Sheet (U.S.)

English