453838-1 ✔ ACTIVE

AMP

TE Internal #: 453838-1

Spare & Wear Tooling, OCEAN

View on TE.com >

Application Tooling > Spare & Wear Tooling



Applicator & Product Style: **OCEAN**

Features

Other

Applicator & Product Style	OCEAN

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 686327-2
M EMPO110F155FK



TE Part # 686327-1
M EMPO110F155FT

Customers Also Bought




TE Part #130171
TERMINAL, PIDG, RT, 12-10 AWG, M5



TE Part #2-520183-2
ULTRA-FAST 250 ASY REC 22-18 TPBR




TE Part #926790-4
PL 250 FLAG REC 1-2.5 MM2 PTP CUZN30 F53



TE Part #1-5435802-5
RIGHT ANGLE DIP SW 4 P SEALED



TE Part #826925-3
03P MODU 2 PIN HDR.



TE Part #926291-1
PL 250 HOUSING FLAG PA 6.6 BLACK



TE Part #690542-2
FEED PAWL-MACHINING



TE Part #453820-6
CRIMPER, WIRE-.070 WIDE F

Documents

Datasheets & Catalog Pages

CRIMPING WHERE FORM MEETS FUNCTION

English

Instruction Sheets

Instruction Sheet (U.S.)

English