

DTS26F25-20PN [V001] ✓ ACTIVE

DEUTSCH | DEUTSCH 38999, DEUTSCH 38999 Series III

TE Internal #: YDTS26F25-20PNV001

Standard Circular Connectors, Cable-to-Panel, 30 Position,
Sealable, Wire & Cable, Power & Signal, Panel Mount, Electroless
Nickel, Aluminum 6061-T6

[View on TE.com >](#)



Connectors > Circular Connectors > Standard Circular Connectors > Straight Plug: D38999, 25-20 Insert, Electroless Nickel Plating



Connector System: **Cable-to-Panel**

Number of Positions: **30**

Sealable: **Yes**

Connector & Contact Terminates To: **Wire & Cable**

Contact Current Rating (Max): **43 A**

[All Straight Plug: D38999, 25-20 Insert, Electroless Nickel Plating \(61\)](#)

Features

Product Type Features

Product Type	Connector
Connector System	Cable-to-Panel
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Plug
Shell Type	Straight Plug

Configuration Features

Number of Positions	30
Number of Power Positions	20
Number of Signal Positions	10
Contacts Preloaded	No

Body Features

Shell Plating Material	Electroless Nickel
Shell Base Material	Aluminum 6061-T6
Circular Connector Insulation Material Type	Hard Dielectric/Silicone
Hermetically Sealed	No



Contact Features

Contact Current Rating (Max)	43 A
Reverse Gender	No
Contact Layout Arrangement	25 – 20
Circular Connector Contact Type	Pin

Mechanical Attachment

Connector Mounting Type	Panel Mount
Polarization Code	N
Mating Alignment Type	Keyed
Mating Retention	With

Housing Features

Circular Connector Shell Size	25
Alignment Keyed	Clocking

Dimensions

Wire Size	5.26 – 8.37 mm ²
-----------	-----------------------------

Usage Conditions

Operating Temperature Range	-65 – 200 °C[-85 – 392 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
Shielded	Yes

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Pb (1.2% in Contact Lead-Copper Alloy) Decamethylcyclpentasiloxane (D5) (5% in Insert subassembly)

Article Safe Usage Statements:



Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-D38999-DTS2K
D38999: Square Flange, 25-20 insert



TE Part # CAT-D38999-DTS11B
D38999: Jam Nut, 25-20 Insert, Electroless Nickel Plating

Also in the Series | DEUTSCH 38999



Standard Circular Connectors(12501)

Also in the Series | DEUTSCH 38999 Series III



Standard Circular Connectors(37354)

Customers Also Bought



TE Part #38943-16L
CONT SOC ASSY



TE Part #38943-20L
CONTACTS (=724-0007-20)



TE Part #38941-20L
CONT PIN



TE Part #YDTS24T25-20SNV001
RECP ASSY



TE Part #YDTS26F15-05PBV001
PLUG ASSY



TE Part #YDTS26W13-04PDV001
PLUG ASSY



TE Part #38941-16
CONTACTS



TE Part #38943-12L
CONTACT T12 FEMELLE (= 724-0007-12)



TE Part #YACT24JB35PCV00100
JAM NUT RECEPTACLE



TE Part #YACT24JC35PAV00100
JAM NUT RECEPTACLE

Documents

Product Drawings

[PLUG ASSY](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_YDTS26F25-20PNV001_D.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_YDTS26F25-20PNV001_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_YDTS26F25-20PNV001_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[DEUTSCH DTS Series Connectors for 38999 QRG](#)

English