

BU-P2249-C-XX

(Test Lead, Male BNC with Strain Reliefs, RG-58C/U)



- Mueller's BU-P2249-C is a test lead with male BNC connectors and strain reliefs on each end of an RG-58C/U cable.
- Wire center conductor is 20 AWG (19x33) tinned copper, and shield is tinned copper braid (95% coverage).

Material: Wire insulation PVC

Male BNC body Tarnish-resistant, nickel-plated brass

Center contact Gold-plated brass

Insulator PTFE

Strain relief Molded PVC

Rating: Impedance 50 Ohms

Capacitance per foot 30.8 pf

Power loss 0.40 dB per 100' @ 1 MHz

Voltage Hands-free testing to 500 VRMS

Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524

Temperature $-40^{\circ}\text{C} (-40^{\circ}\text{F}) \text{ to } 85^{\circ}\text{C} (185^{\circ}\text{F})$

- Length: The "XX" in the part number represents the length in inches. Standard Lengths: 6", 12", 24", 36", 48", 60", 72", 120", 180", 240", 300", 600"
- RoHS 3 Compliant