

Fuseholders 6 x 30 mm (1¼"x¼")



16A 250Vac (max fuse rating*) T-55 to T+70 (ambient)

Maximum dissipation wattage: 2.5W

UL 94V2 UL file E92075 CSA file LR44770

These products comply with safety category PC2

*Users should be aware of the de-rating factors published by specialist manufacturers of fuses


Fuseholders with in-line termination have combination (4.8 / 6.3) terminals. It has not been possible to show both views here. Units with right angle terminals have user specified end terminals and combination mid-body terminals



M873
Cover for C & T terminals



A0035 00
In-line 6 x 30 1¼ x ¼ fuseholder
Call factory for rating details



TERMINAL	BODY AND CAP	PANEL HOLE	DIMENSIONS (mm)
<p>C</p> <p>6.3 x 0.8</p>	<p>0345 (C terminal shown)</p> <p>Ⓢ Ⓝ Ⓟ Ⓡ Ⓢ Ⓡ</p>	<p>RA</p> <p>Panel thickness 0.8 - 2.0mm for snap-in 0.8 - 4.5mm for nut fixing</p>	<p>0345 (C terminal shown)</p>
<p>D</p> <p>6.3 x 0.8 Right angle</p>	<p>0345 (D terminal shown)</p> <p>Ⓢ Ⓝ Ⓟ Ⓡ Ⓢ Ⓡ</p>	<p>RD</p> <p>Panel thickness 0.8 - 2.0mm for snap-in 0.8 - 4.5mm for nut fixing</p>	<p>0345 (D terminal shown)</p>
<p>T</p> <p>4.8 x 0.8 Solder</p>	<p>0347 (T terminal shown)</p> <p>Ⓢ Ⓝ Ⓟ Ⓡ Ⓢ Ⓡ</p>	<p>RD</p> <p>Panel thickness 0.8 - 2.0mm for snap-in 0.8 - 4.5mm for nut fixing</p>	<p>0347 (C terminal shown)</p>
<p>U</p> <p>4.8 x 0.8 Right angle solder</p>	<p>0347 (U terminal shown)</p> <p>Ⓢ Ⓝ Ⓟ Ⓡ Ⓢ Ⓡ</p>	<p>RD</p> <p>Panel thickness 0.8 - 2.0mm for snap-in 0.8 - 4.5mm for nut fixing</p>	<p>0347 (D terminal shown)</p>