




Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Covers



Connector Cover Type: **Strain Relief**

Number of Positions: **50**

Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Product Type Features

Product Type	Accessory
Connector Cover Type	Strain Relief

Configuration Features

Number of Positions	50
---------------------	----

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Method	Kit, Package
Packaging Quantity	100

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 229974-1
ASSY, PLUG, 50 POS, B SLOT

Also in the Series | CHAMP Docking Connectors

D-Sub Covers(28)

D-Sub Locking & Mounting(29)

Docking Connector Guide Hardware(5)

Docking Connectors(31)

IDC D-Sub Connectors(79)

PCB D-Sub Connectors(1)

Customers Also Bought



TE Part #178305-2
DYNAMIC D3100D HDR H 10P ASSY
AU038



TE Part #6469048-1
HMZD 4PR RA HDR 80P ASSY LF



TE Part #6469025-1
HM-ZD 2PR HDR 40P 2.5MM



TE Part #173860-1
LOW & MEDIUM POWER HEADER



TE Part #174977-2
SIGNAL HEADER



TE Part #53880-2
CONTACT,PWR LK,SRS2,STRIP,CRMP



TE Part #5177578-1
CHAMP PLUG CABLE COVER KIT

Documents

Product Drawings

COVER KIT TAPERED 50 POS

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_5552560-5_O.2d_dxf.zip

English

Customer View Model

ENG_CVM_5552560-5_O.3d_igs.zip

English

Customer View Model

ENG_CVM_5552560-5_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.