T4031017031-000 ✔ ACTIVE


M8 Connector

TE Internal #: T4031017031-000

Standard Circular Connectors, Wire-to-Board, 3 Position, Sealable, Wire & Cable, Signal, Nickel, Brass, A Polarization Code, M8 Connector

View on TE.com >

Connectors > Circular Connectors > Standard Circular Connectors > M8 Panel Mount Solder Cups




Connector System: **Wire-to-Board**

Number of Positions: **3**

Sealable: **Yes**

Connector & Contact Terminates To: **Wire & Cable**

Contact Current Rating (Max): **3 A**

All M8 Panel Mount Solder Cups (8)

Features

Product Type Features

Prewired	No
Product Type	Connector
Accessory Color	Black
Assembly Type	Electrical Connector
Connector System	Wire-to-Board
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Receptacle
Shell Type	Metal

Configuration Features

Keying & Polarized Position Locations	A
Factory Installed Backshell	No
Keying	A

Number of Positions	3
Number of Power Positions	0
Number of Signal Positions	3
Contacts Preloaded	Yes

Electrical Characteristics

Operating Voltage	60 VAC

Body Features

Peripheral Seal Material	Silicone
Environmental Protection	IP67
O-Ring Material	Silicone
Environmental Protection Type	Sealed
Shell Plating Material	Nickel
Shell Base Material	Brass
Circular Connector Insulation Material Type	Polyamide 67 GF30

Contact Features

Contact Current Rating (Max)	3 A
Reverse Gender	No
Circular Connector Contact Type	Socket

Mechanical Attachment

Polarization Code	A
Mating Alignment Type	Keyed

Housing Features

Circular Connector Shell Size	12.6

Usage Conditions

IP Dust Sealing Level	6
IP Water Sealing Level	IP67
Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]

Operation/Application

Circuit Application	Signal
Shielded	No

Industry Standards

UL Flammability Rating	UL 94HB

Packaging Features

Packaging Quantity	1

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Pb (4% in Component Part) **Article Safe Usage Statements:** Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # T4011008031-000
M8,SCREW, MALE,S,UNSHIELD,3P, GOLD

Also in the Series | M8 Connector



M8/M12 Cable Assemblies(135)



Standard Circular Connectors(72)

Customers Also Bought




TE Part #T4011008031-000
M8,SCREW, MALE,S,UNSHIELD,3P, GOLD




TE Part #T4030014041-000
M8.MLE.PNLREAR.4POS.STR.



TE Part #4-794618-8
18P MICRO MNL ASSY R/A HDR LF



TE Part #2-2176370-7
RQ 0603 806R 0.1% 10PPM 5K RL



TE Part #2176315-2
MELF SMA_A 120R 0.1% 15PPM 0204 0.4W



TE Part #51864-9
TERMINAL,PIDG R IR 14 10



TE Part #4-1462037-2
IM04GR=IM RELAY 140mW 6V



TE Part #TAD1453A201-001
M12D4-MS-FS-TPE-24SH-TEAL-0.5M



TE Part #1534796-2
AMP DUOPLUG MK2 CONNECTOR 2P



TE Part #NB15272001
CRN-1/4-0-STK

Documents

Product Drawings

M8.FMLE.PNLREAR.3POS.STR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_T4031017031-000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_T4031017031-000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_T4031017031-000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

M8 / M12 Connector System Catalog

English

Product Specifications

Application Specification

English

Application Specification

English