

# DTS26Z21-35PA [V001] ✓ ACTIVE

DEUTSCH | DEUTSCH 38999 Series III

TE Internal #: YDTS26Z21-35PAV001

Standard Circular Connectors, Cable-to-Panel, 79 Position,  
Sealable, Wire & Cable, Signal, Panel Mount, Black Zinc Nickel,  
DEUTSCH 38999 Series III

[View on TE.com >](#)



Connectors > Circular Connectors > Standard Circular Connectors > D38999: Straight Plug, 21-35 Insert



Connector System: **Cable-to-Panel**

Number of Positions: **79**

Sealable: **Yes**

Connector & Contact Terminates To: **Wire & Cable**

Contact Current Rating (Max): **5 A**

[All D38999: Straight Plug, 21-35 Insert \(60\)](#)

## Features

### Product Type Features

|                                   |                |
|-----------------------------------|----------------|
| Product Type                      | Connector      |
| Connector System                  | Cable-to-Panel |
| Sealable                          | Yes            |
| Connector & Contact Terminates To | Wire & Cable   |
| Circular Connector Type           | Plug           |
| Shell Type                        | Straight Plug  |

### Configuration Features

|                            |    |
|----------------------------|----|
| Number of Positions        | 79 |
| Number of Power Positions  | 0  |
| Number of Signal Positions | 79 |
| Contacts Preloaded         | No |

### Body Features

|   |                          |
|---|--------------------------|
| Shell Plating Material                      | Black Zinc Nickel        |
| Shell Base Material                         | Aluminum 6061-T6         |
| Circular Connector Insulation Material Type | Hard Dielectric/Silicone |
| Hermetically Sealed                         | No                       |



### Contact Features

|                                 |         |
|---------------------------------|---------|
| Contact Current Rating (Max)    | 5 A     |
| Reverse Gender                  | No      |
| Contact Layout Arrangement      | 21 – 35 |
| Circular Connector Contact Type | Pin     |

### Mechanical Attachment

|                         |             |
|-------------------------|-------------|
| Connector Mounting Type | Panel Mount |
| Polarization Code       | A           |
| Mating Alignment Type   | Keyed       |
| Mating Retention        | With        |

### Housing Features

|                               |          |
|-------------------------------|----------|
| Circular Connector Shell Size | 21       |
| Alignment Keyed               | Clocking |

### Dimensions

|           |                           |
|-----------|---------------------------|
| Wire Size | .08 – .33 mm <sup>2</sup> |
|-----------|---------------------------|

### Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -65 – 200 °C[-85 – 392 °F] |
|-----------------------------|----------------------------|

### Operation/Application

|                     |        |
|---------------------|--------|
| Circuit Application | Signal |
| Shielded            | Yes    |

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|   |  |
|---|--|
| EU RoHS Directive 2011/65/EU                  | Compliant with Exemptions  |
| EU ELV Directive 2000/53/EC                   | Compliant with Exemptions  |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold   |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2022 (224)<br>Candidate List Declared Against: JUNE 2022 (224)<br>SVHC > Threshold:<br>Pb (1.2% in Contact Lead-Copper Alloy)<br>Decamethylcyclpentasiloxane (D5) (5% in Insert subassembly) |

Article Safe Usage Statements:



Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # CAT-D38999-DTS8X  
D38999: Square Flange, 21-35 insert



TE Part # CAT-D38999-DTS17M  
Jam Nut: D38999, 21-35 Insert, Black Zinc Nickel Plating

### Also in the Series | DEUTSCH 38999 Series III



Standard Circular Connectors(37354)

### Customers Also Bought



TE Part #5039244037  
DR-25-1-0-SP



TE Part #YDTS20Z21-35PAV001  
RECP ASSY



TE Part #YDTS20F17-26ANV001  
RECP ASSY



TE Part #YDTS24W25-43SAV001  
RECP ASSY



TE Part #YDTS26Z11-99PAV001  
PLUG ASSY




TE Part #YDTS26Z21-35PNV001  
PLUG ASSY




TE Part #YDTS26Z23-55SNV001  
PLUG ASSY



TE Part #ZPF000000000007383  
983-0S 16-10 SN



TE Part #EF8570-000  
R85049/88-19Z03



TE Part #ZPF000000000204539  
DTS 26 B 21-75 SN-A1055

## Documents

### Product Drawings

[PLUG ASSY](#)

English

### Datasheets & Catalog Pages

[DEUTSCH MIL-DTL-38999 CIRCULAR CONNECTORS](#)

English