

DTS26F19-32SN [V001]

✓ ACTIVE

DEUTSCH | DEUTSCH 38999, DEUTSCH 38999 Series III

TE Internal #: YDTS26F19-32SNV001

Standard Circular Connectors, Cable-to-Panel, 32 Position,
Sealable, Wire & Cable, Signal, Panel Mount, Electroless Nickel,
DEUTSCH 38999 Series III

[View on TE.com >](#)



Connectors > Circular Connectors > Standard Circular Connectors > Straight Plug: D38999, 19-32 Insert, Electroless Nickel Plating



Connector System: **Cable-to-Panel**
Number of Positions: **32**
Sealable: **Yes**
Connector & Contact Terminates To: **Wire & Cable**
Contact Current Rating (Max): **7.5 A**

[All Straight Plug: D38999, 19-32 Insert, Electroless Nickel Plating \(70\)](#)

Features

Product Type Features

Product Type	Connector
Assembly Type	Electrical Connector
Connector System	Cable-to-Panel
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Plug
Shell Type	Straight Plug

Configuration Features

Keying & Polarized Position Locations	N
Factory Installed Backshell	No
Keying	Key Polarization N
Number of Positions	32
Number of Power Positions	0
Number of Signal Positions	32
Contacts Preloaded	No

Electrical Characteristics



Operating Voltage	600 VAC
Voltage	1800 Vrms

Body Features

Environmental Protection	Yes
Feedthrough Type	No
Environmental Protection Type	Elastomer Sealed
Entry Style	Rear Insertion
Fluid Type	Coolanol 25, M2-V, MIL-DTL-5624 (JP-4,JP-5), MIL-DTL-83133 (JP-8), MIL-PRF-23699, MIL-PRF-5606, MIL-PRF-7808, SEA-AMS1424 Type I
Shell Plating Material	Electroless Nickel
Shell Base Material	Aluminum
Circular Connector Insulation Material Type	Hard Dielectric/Silicone
Hermetically Sealed	No

Contact Features

Contact Quantity (Size 20)	32
Contact Current Rating (Max)	7.5 A
Reverse Gender	No
Contact Layout Arrangement	19 – 32
Circular Connector Contact Type	Socket

Mechanical Attachment

Mating Retention Type	Threaded
Panel Mount Feature	Without
Connector Mounting Type	Panel Mount
Polarization Code	N
Mating Alignment Type	Keyed
Mating Retention	With

Housing Features

Circular Connector Shell Size	19
Alignment Keyed	Clocking

Dimensions

Accepts Wire Insulation Diameter Range	1.02 – 2.11 mm[.04 – .083 in]
--	-------------------------------

Assembly Length	31 mm[1.22 in]
Wire Size	24 – 20 AWG

Usage Conditions

Fluid Resistance	Yes
Operating Temperature Range	-65 – 200 °C[-85 – 392 °F]

Operation/Application

Durability Rating	500 Cycles
Circuit Application	Signal

Packaging Features

Packaging Quantity	1
--------------------	---

Other

Position Locations Omitted	All
----------------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Pb (1.2% in Contact Lead-Copper Alloy) Decamethylcyclopentasiloxane (D5) (5% in Insert subassembly) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits



as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # CAT-D38999-DTS1W
D38999: Square Flange, 19-32 insert



TE Part # CAT-D38999-DTS10L
D38999: Jam Nut, 19-32 Insert, Electroless Nickel Plating




TE Part # YDTS21H19-32CNV001
HERM RECP



TE Part # YDTS21H19-32PNV001
HERM RECP




TE Part # YDTS21H19-32XNV001
HERM RECP



TE Part # YDTS23H19-32CNV001
HERM RECP



TE Part # YDTS23H19-32PNV001
HERM RECP



TE Part # YDTS23H19-32XNV001
HERM RECP



TE Part # YDTS20H19-32CN0000
HERM RECP




TE Part # YDTS20H19-32PN0000
HERM RECP




TE Part # YDTS20H19-32XN0000
HERM RECP



TE Part # YDTS20N19-32CNV001
HERM RECP



TE Part # YDTS20N19-32PNV001
HERM RECP ASM




TE Part # YDTS20N19-32XNV001
HERM RECP




TE Part # YDTS20Y19-32CNV001
HERM RECP



TE Part # YDTS20Y19-32PNV001
HERM RECP



TE Part # YDTS20Y19-32XNV001
HERM RECP



TE Part # YDTS21H19-32CN0000
DTS21H19-32CN



TE Part # YDTS21H19-32PN0000
DTS21H19-32PN



TE Part # YDTS21H19-32XN0000
DTS21H19-32XN

Also in the Series | **DEUTSCH 38999**



Standard Circular Connectors(12501)

Also in the Series | **DEUTSCH 38999 Series III**



Standard Circular Connectors(37354)

Customers Also Bought



TE Part # YDTS26F17-06PNV001
PLUG ASSY



TE Part # YDTS26F23-35PNV001
PLUG ASSY



TE Part # YDTS26F17-26SNV001
PLUG ASSY



TE Part # YDTS26F21-41SNV001
PLUG ASSY



TE Part #GA30K6A1B
DISCRETE NTC SERIES I

TE Part #10220788-00
9216-0405041300: CTO-12000000-06

TE Part #10226868-00
9216-0605041300: CTO-12000000-06

TE Part #10227131-00
9216-2305041300: CTO-12000000-06

TE Part #10227128-00
9216-2705041300: CTO-12000000-06

Documents

Product Drawings

PLUG ASSY

English

Datasheets & Catalog Pages

DEUTSCH MIL-DTL-38999 Connectors Quick Reference Guide

English