

DTS24W15-19PN [V001]

✓ ACTIVE

DEUTSCH | DEUTSCH 38999 Series III

TE Internal #: YDTS24W15-19PNV001

Standard Circular Connectors, Cable-to-Panel, 19 Position,
Sealable, Wire & Cable, Signal, Panel Mount, Cadmium O.D.,
Aluminum, N Polarization Code

[View on TE.com >](#)



Connectors > Circular Connectors > Standard Circular Connectors > Jam Nut: D38999, 15-19 Insert



Connector System: **Cable-to-Panel**
Number of Positions: **19**
Sealable: **Yes**
Connector & Contact Terminates To: **Wire & Cable**
Contact Current Rating (Max): **7.5 A**

[All Jam Nut: D38999, 15-19 Insert \(64\)](#)

Features

Product Type Features

Product Type	Connector
Connector System	Cable-to-Panel
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Receptacle
Shell Type	Jam Nut Receptacle

Configuration Features

Number of Positions	19
Number of Power Positions	0
Number of Signal Positions	19
Contacts Preloaded	Yes

Body Features

Shell Plating Material	Cadmium O.D.
Shell Base Material	Aluminum
Circular Connector Insulation Material Type	Hard Dielectric/Silicone
Hermetically Sealed	No



Contact Features

Contact Current Rating (Max)	7.5 A
Reverse Gender	No
Contact Layout Arrangement	15 – 19
Circular Connector Contact Type	Pin

Mechanical Attachment

Connector Mounting Type	Panel Mount
Polarization Code	N
Mating Alignment Type	Keyed
Mating Retention	With

Housing Features

Circular Connector Shell Size	15
Alignment Keyed	Clocking

Dimensions

Wire Size	.2 – .52 mm ²
-----------	--------------------------

Usage Conditions

Operating Temperature Range	-65 – 175 °C[-85 – 347 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
Shielded	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Cd (2.6% in Plating) Pb (1.2% in Pin Copper Alloy) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.



Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # YDTS26W15-19SNV001
PLUG ASSY

Also in the Series | DEUTSCH 38999 Series III

Standard Circular Connectors(37354)

Customers Also Bought

TE Part #60894-1
RECEPT,PIDG FASTON 22-18 110

TE Part #1623729-9
BCHE 17 W 1R0 10%

TE Part #YDTS26W15-18PNV001
PLUG ASSY

TE Part #YDTS26W15-19SNV001
PLUG ASSY





TE Part #YDTS26W15-97PNV001
PLUG ASSY




TE Part #YDTS20W15-97SNV001
RECP ASSY



TE Part #YDTS26W11-02SBV001
PLUG ASSY



TE Part #EK1188-000
55A1826-22-9/96-9



TE Part #134710-000
HRHT-2/3

Documents

Product Drawings

RECP ASSY

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_YDTS24W15-19PNV001_99.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_YDTS24W15-19PNV001_99.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_YDTS24W15-19PNV001_99.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

DEUTSCH MIL-DTL-38999 CIRCULAR CONNECTORS

English