ACT26JJ20PD [V001] ACTIVE

DEUTSCH | DEUTSCH 38999 Series III Composite Connectors

TE Internal #: YACT26JJ20PDV00100

Standard Circular Connectors, Cable-to-Panel, 30 Position,

Sealable, Wire & Cable, Power & Signal, DEUTSCH 38999 Series III

Composite Connectors

View on TE.com >



Connectors > Circular Connectors > Standard Circular Connectors > Straight Plug D38999, J20 Insert



Connector System: Cable-to-Panel

Number of Positions: 30

Sealable: Yes

Connector & Contact Terminates To: Wire & Cable

Contact Current Rating (Max): 43 A

All Straight Plug D38999, J20 Insert (60)

Features

Product Type Features

Product Type	Connector
Assembly Type	Electrical Connector
Connector System	Cable-to-Panel
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Plug
Shell Type	Straight Plug

Configuration Features

Keying & Polarized Position Locations	D
Factory Installed Backshell	No
Keying	Key Polarization D
Number of Positions	30
Number of Power Positions	20
Number of Signal Positions	10
Contacts Preloaded	No

Electrical Characteristics



Voltage	1000 Vrms
Operating Voltage	300 VAC
ody Features	
Feedthrough Type	No
Environmental Protection Type	Elastomer Sealed
Entry Style	Rear Insertion
Environmental Protection	Yes
Weight	35.7 g[.0788 lb]
Fluid Type	Coolanol 25, M2-V, MIL-DTL-5624 (JP-4,JP-5), MIL-DTL-83133 (JP-8), MIL-PRF-23699, MIL-PRF-5606, MIL-PRF-7808, SEA-AMS1424 Type I
Shell Plating Material	Cadmium, O.D.
Shell Base Material	Composite
Circular Connector Insulation Material Type	Hard Dielectric/Silicone
Hermetically Sealed	No
Contact Features	
Contact Quantity (Size 20)	10
Contact Quantity (Size 16)	13
Contact Quantity (Size 22D)	13
Contact Quantity (Size 12 Coax)	4
Contact Quantity (Size 8 Databus)	3
Contact Current Rating (Max)	43 A
Reverse Gender	No
Contact Layout Arrangement	J20
Circular Connector Contact Type	Pin
Mechanical Attachment	
Mating Retention Type	Triple Start Threaded
Panel Mount Feature	Without
Connector Mounting Type	Panel Mount
Polarization Code	D
Mating Alignment Type	Keyed
Mating Retention	With

Housing Features



Circular Connector Shell Size	25
Alignment Keyed	Clocking
Dimensions	
Assembly Length	31.5 mm[1.24 in]
Wire Size	5.26 – 8.37 mm ²
Usage Conditions	
Fluid Resistance	Yes
Operating Temperature Range	-65 – 200 °C[-85 – 392 °F]
Operation/Application	
Durability Rating	500 Cycles
Circuit Application	Power & Signal
Shielded	Yes
Packaging Features	
Packaging Quantity	1
Other	

AII

Product Compliance

Position Locations Omitted

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Cd (3.45% in Plating) Pb (1.2% in Contact Lead-Coper Alloy) Decamethylcyclopentasiloxane (D5) (5% in Insert Subassembly) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Standard Circular Connectors, Cable-to-Panel, 30 Position, Sealable, Wire & Cable, Power & Signal, DEUTSCH 38999 Series III Composite Connectors



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Compatible Parts







Also in the Series | DEUTSCH 38999 Series III Composite Connectors



Customers Also Bought










Standard Circular Connectors, Cable-to-Panel, 30 Position, Sealable, Wire & Cable, Power & Signal, DEUTSCH 38999 Series III Composite Connectors













Documents

Product Drawings
STRAIGHT PLUG

English

Datasheets & Catalog Pages

DEUTSCH MIL-DTL-38999 Connectors Quick Reference Guide

English