



Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Backshells & Clamps > CRIMP FLANGE FOR SIZE 1-3STD/1-4QL SHELL



D-Shaped Connector Accessories: **Crimp Flange**  
Shielded: **Yes**  
Connector & Contact Terminates To: **Wire & Cable**  
Operating Temperature Range: **-40 – 90 °C [-40 – 194 °F]**

**All CRIMP FLANGE FOR SIZE 1-3STD/1-4QL SHELL (14)**

Features

Product Type Features

|                                   |                       |
|-----------------------------------|-----------------------|
| Clam Shell Length                 | Standard              |
| Grommets                          | Without               |
| Slide Latch                       | Without               |
| Product Type                      | Backshell/Cable Clamp |
| D-Shaped Connector Accessories    | Crimp Flange          |
| Connector & Contact Terminates To | Wire & Cable          |

Mechanical Attachment

|                          |      |
|--------------------------|------|
| Screw & Hole Thread Size | None |
|--------------------------|------|

Usage Conditions

|                             |                           |
|-----------------------------|---------------------------|
| Operating Temperature Range | -40 – 90 °C[-40 – 194 °F] |
|-----------------------------|---------------------------|

Operation/Application

|          |     |
|----------|-----|
| Shielded | Yes |
|----------|-----|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|                              |                           |
|------------------------------|---------------------------|
| EU RoHS Directive 2011/65/EU | Compliant with Exemptions |
| EU ELV Directive 2000/53/EC  | Not Yet Reviewed          |



|                                               |                                                                                                                                                                                                                                                                                                                                                                                                                                |
|-----------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold                                                                                                                                                                                                                                                                                                                                                                                           |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2022 (224)<br>Candidate List Declared Against: JUNE 2022 (224)<br>SVHC > Threshold:<br>Pb (3.5% in Component Part)<br><b>Article Safe Usage Statements:</b><br>Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                                                                                                                                                                                                                                                                                                                            |
| Solder Process Capability                     | Not reviewed for solder process capability                                                                                                                                                                                                                                                                                                                                                                                     |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




Also in the Series | Rail D-Sub Backshells



Crimp D-Sub Connectors(10)



D-Sub Backshells & Clamps(143)



D-Sub Connector Contacts(5)

Customers Also Bought



TE Part #1-2308340-3  
FULL METAL HOODS SIZE 1-3 (RAW 180 DEG)



TE Part #1-2308341-3  
FULL METAL HOODS SIZE 2-3 (RAW 180 DEG)



TE Part #204519-2  
AMPLIMITE,ASY,PLUG,STD,90,4



TE Part #204506-1  
RECEPT ASSY,62 POSN,AMPLIMITE



TE Part #CF0364-000  
204W201-25-0



TE Part #1757824-8  
AMPLIMITE,ASY,RCPT,STD,90,ZN,2, CONT




TE Part #204518-2  
RECEPT ASSY,62 POSN,AMPLIMITE



TE Part #1393560-5  
C42334A 383C911=SUB D BOLZEN A



TE Part #31088  
BUDGET R 22-16COMM 22-18MIL 2



TE Part #284303-000  
B-020-22-N

Documents

Product Drawings

CRIMP FLANGE 8 SMALL

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1-2308349-8\_A.2d\_dxf.zip





English

Customer View Model

[ENG\\_CVM\\_CVM\\_1-2308349-8\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1-2308349-8\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Rail D-Sub Backshells Flyer](#)

English