




CIRH

TE Internal #: Y5015-000000100125

Standard Circular Connectors, Wire-to-Wire / Cable-to-Cable, 7 Position, Wire & Cable, Power & Signal, Panel Mount, Reverse Gender, CIRH

[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors > 4 HOLE FLANGE RECEPTACLE REAR PNL MALE



Connector System: **Cable-to-Cable, Wire-to-Wire**

Number of Positions: **7**

Connector & Contact Terminates To: **Wire & Cable**

Circuit Application: **Power & Signal**

Connector Mounting Type: **Panel Mount**

All 4 HOLE FLANGE RECEPTACLE REAR PNL MALE (17)

Features

Product Type Features

Product Type	Connector
Accessory Color	Black
Prewired	No
Connector System	Cable-to-Cable, Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Receptacle
Shell Type	Metal

Configuration Features

Factory Installed Backshell	Without
Number of Positions	7
Contacts Preloaded	No

Body Features

Shell Plating Material	Black Chromate Over Zn Cobalt
Shell Base Material	Aluminum Alloy
Circular Connector Insulation Material Type	Low Fire Hazard Rubber

Contact Features



Reverse Gender	Yes
Contact Layout Arrangement	16 – 1
Circular Connector Contact Type	Pin

Mechanical Attachment

Mating Retention Type	Bayonet
Mating Alignment	With
Panel Mount Feature	With
Panel Mount Feature Type	Square Flange
Connector Mounting Type	Panel Mount
Mating Alignment Type	Keyed
Mating Retention	With

Usage Conditions

IP Water Sealing Level	IP67
Operating Temperature Range	-55 – 200 °C[-67 – 392 °F]

Operation/Application

Circuit Application	Power & Signal
Shielded	Yes

Packaging Features

Packaging Quantity	10
--------------------	----

Other

Position Locations Omitted	All
Field Serviceable	Yes

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2019 (197) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-R131-C4967L

Crimp Contact Pin - CIRH

Also in the Series | CIRH



Circular Connector Contact Inserts(15)



Circular Connector Seals(17)



Standard Circular Connectors(71)



Unscreened Circular Connector Backshells & Clamps(55)

Customers Also Bought







TE Part #5-1879213-9
CPF 0402 113R 0.1% 25PPM 1K RL




TE Part #2-2329389-0
PB OFF/ON FC GRE M1 TERM BLU
LED IP68 50



TE Part #5-2176244-5
CRGS0805 5% 33K



TE Part #1624250-8
CGS SL1 R068 5% TAPED



TE Part #9-2176266-2
RU 0402 4K75 0.01% 2PPM 1K RL



TE Part #1SNA290243R1200
DB2.5/5.N.2L

Documents

Product Drawings
FIXED PIN CONNECTOR
French

Datasheets & Catalog Pages
CIRH Brochure
English

Product Specifications
Application Specification
French