

# RNF-100-3/8-2-SP ✓ ACTIVE

RAYCHEM | RAYCHEM RNF-100

TE Internal #: 5053154018

Heat Shrink Tubing, Red, Single Wall, .375 in [9.5 mm] Expanded Inside, .187 in [4.8 mm] Recovered Inside, 2:1 Shrink Ratio, RAYCHEM RNF-100

[View on TE.com >](#)



Heat Shrink Tubing > Single Wall RNF-100 Flat Spool HST



Primary Product Color: **Red**

Wall Type: **Single**

Expanded Inside Diameter (Min): **9.5 mm [ .375 in ]**

Recovered Inside Diameter (Max): **4.8 mm [ .187 in ]**

Shrink Ratio: **2:1**

[All Single Wall RNF-100 Flat Spool HST \(55\)](#)

## Features

### Product Type Features

|                |         |
|----------------|---------|
| Product Family | RNF-100 |
| Wall Type      | Single  |

### Electrical Characteristics

|               |       |
|---------------|-------|
| Voltage (Max) | .6 kV |
|---------------|-------|

### Body Features

|                          |   |
|--------------------------|---|
| Fluid Type               | Gasoline, Hydraulic Fluid, Lubricating Oil, Water |
| Primary Product Color    | Red   |
| Shrink Ratio             | 2:1   |
| Primary Product Material | Irradiated Modified Polyolefin                    |
| Flexibility              | Flexible  |

### Dimensions

|                                      |                              |
|--------------------------------------|------------------------------|
| Recovered Wall Thickness (Tolerance) | .08 mm[.003 in]              |
| Recovered Wall Thickness (Nominal)   | .64 mm[.025 in]              |
| Expanded Inside Diameter (Min)       | 9.5 mm[.375 in]              |
| Recovered Inside Diameter (Max)      | 4.8 mm[.187 in]              |
| Heat Shrink Tubing Size Range        | 4.8 – 9.5 mm[.187 – .375 in] |



### Usage Conditions

|                                 |  |
|---------------------------------|--|
| Shrink Temperature (Min)        | 95 °C  |
| Fluid Resistance                | Splash Protection                                  |
| Heat Shrink Tubing Flammability | Flame-Retardant                                    |
| Operating Temperature Range     | -55 – 135 °C                                       |
| Heat Shrink Tubing Resistance   | Abrasion, Fluids, Mechanical Damage, Strain Relief |
| Recovery Temperature            | 121 °C   |

### Product Availability

|                   |        |
|-------------------|--------|
| Applicable Region | Global |
|-------------------|--------|

### Packaging Features

|                  |     |
|------------------|-----|
| Packaging Method | Box |
|------------------|-----|

### Other

|                                   |                |
|-----------------------------------|----------------|
| Meets Low Outgassing Requirements | No             |
| Product Source                    | Czech Republic |

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


|   |   |
|---|---|
| EU RoHS Directive 2011/65/EU                  | Compliant   |
| EU ELV Directive 2000/53/EC                   | Compliant   |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold   |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2022 (224)<br>Candidate List Declared Against: JUNE 2022 (224)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.  |
| Solder Process Capability                     | Not applicable for solder process capability  |

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits

as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Also in the Series | RAYCHEM RNF-100




Heat Shrink Tubing(985)



Power Cable Tubing & Accessories(8)

## Customers Also Bought



TE Part #165938-000  
202K121-25/86-0



TE Part #5053144070  
Single Wall RNF-100 Flat Spool HST



TE Part #5052944058  
RNF-100-3/32-0-SP




TE Part #1623730-4  
BCHE 4 W 15R 5%



TE Part #5053194052  
RNF-100-1/2-0-SP



TE Part #5053094080  
RNF-100-1/4-0-SP



TE Part #405617-000  
B-044-24-N



TE Part #5053174023  
RNF-100-3/8-6-SP



TE Part #E45478-000  
1330-0607-T200

## Documents

[Datasheets & Catalog Pages](#)  
[RNF-100 Pages from 9-1773447-9](#)



English

---

**Product Specifications**

**Quality Specification**

English

---

**Product Environmental Compliance**

**Safety Datasheet**

English

**Safety Datasheet**

English

**Safety Datasheet**

**Safety Datasheet**

**Safety Datasheet**

English

**Safety Datasheet**

French

**Safety Datasheet**

German

**Safety Datasheet**

**Safety Datasheet**

**Safety Datasheet**

**Safety Datasheet**

**Safety Datasheet**

English

**Safety Datasheet**