

VERSAFLEX-40-0-SP ✓ ACTIVE

RAYCHEM | RAYCHEM VERSAFLEX


TE Internal #: CH01974001

Heat Shrink Tubing, Black, Braid Wall, Polyester, Non-Flame-Retardant, Box, -50 – 150 °C, Resistant To Mechanical Damage, Flexible, RAYCHEM VERSAFLEX

[View on TE.com >](#)



Heat Shrink Tubing



Primary Product Color: **Black**

Wall Type: **Braid**

Primary Product Material: **Polyester**

Heat Shrink Tubing Flammability: **Non-Flame-Retardant**

Packaging Method: **Box**

Features

Product Type Features

Product Family	VERSAFLEX
Wall Type	Braid

Body Features

Primary Product Color	Black
Primary Product Material	Polyester
Flexibility	Flexible

Dimensions

Heat Shrink Tubing Size Range	30 – 50 mm[1.181 – 1.968 in]
-------------------------------	------------------------------

Usage Conditions

Heat Shrink Tubing Flammability	Non-Flame-Retardant
Operating Temperature Range	-50 – 150 °C
Heat Shrink Tubing Resistance	Mechanical Damage

Product Availability

Applicable Region	Global
-------------------	--------

Packaging Features

Packaging Method	Box
------------------	-----

Other



Meets Low Outgassing Requirements	No
Product Source	Europe

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUN 2020 (209) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CJ2087-000
[HL2010E-KIT-120V](#)



TE Part # EG1114-000
[CV1981-ST-230V1600W-EU](#)

Also in the Series | **RAYCHEM VERSAFLEX**



Heat Shrink Tubing(30)

Customers Also Bought



TE Part #DT04-2P
DEUTSCH DT Series Housings & Connectors




TE Part #W2S
DEUTSCH DT WEDGELOCKS



TE Part #282104-1
AMP SUPERSEAL 1.5MM,
CONNECTOR HOUSING



TE Part #206070-8
CABLE CLAMP KIT #17



TE Part #281934-2
SINGLE WIRE SEAL



TE Part #0460-202-16141
DEUTSCH SOLID CONTACTS

Documents

Datasheets & Catalog Pages

[VERSAFLEX - Expandable Braided Polyester Sleeving](#)

English

Product Specifications

[Quality Specification](#)

English