



#### **Features**

- Sealed housing conforms to IP6K9K
- Dual-Coil monostable high performance relay with optional auxiliary contact
- Up to 30G shock & 10G vibration resistant
- Military grade performance
- Wide variety of configuration options for individual needs
- Meets the requirements of MIL-R-6106

#### **Applications**

- Truck
- Bus
- Ground support vehicles
- Construction and agricultural vehicles
- Power Distribution
- Aviation industry
- Military

# KISSLING HIGH PERFORMANCE RELAYS

Series 26 / 350A | 500A - from TE Connectivity (TE)

KISSLING 26 series dual coil relays are developed using our competence and expertise gathered over decades of manufacturing to meet demanding operating requirements.

This dual coil system relay features extremely high shock and vibration resistance predominantly from careful design and an optimized magnetic circuit. The sealing technology used in these relays meet both the IP67 and IP69K (Steam pressure cleaning) protection standard. This relay series is well suited for various applications in severe commercial, military and aviation applications.

Other important advantages are low heat generation in the contact area based on low contact voltage drop, a compact design, low holding et, silver alloy contact material and the use of mechanical and high thermal stability insulating compounds. Both the terminals and housing is corrosion resistant.

These relays are available with a wide variety of configuration options including contact configurations (NO, NC) coil voltages (12V, 24/28V) and various bracket styles to meet your installation conditions. Also available are optional suppression devices to eliminate electromagnetic interference at the coils and optional auxiliary contacts.

## **Specification**

Technical Data	350	AC	į						
Temperature range	-55	s°C to +130°C	-55°C to +74°C						
Max. Altitude rating	50.	.000 ft							
Protection	IEC	IEC 60529 & DIN 40050-9, IP67 (0,2 bar; 1min) & IP6K9K							
Shock	30	30G - 11msec   MIL-STD-202							
Vibration	100	10G (10-2000Hz)   MIL-STD-202							
Acceleration	150	15G							
Thread sizes	M4	= 2.0-2.2Nm / M12 = 18-	22Nm						
Wire section	mir	n. 150mm2 / 0.233 sq.inc	:h / MCM 300 r	min. 240mm2 / 0.372 sq.inch / MCM 500					
Mounting position	opt	tional							
Electrical Characteristics		350A			500A				
Min. Insulation Resistance		100ΜΩ			100ΜΩ				
After live or environmenta		50ΜΩ			50ΜΩ				
Dielectric withstanding vo	Dielectric withstanding voltage		Z		1050VAC / 1min at 50Hz				
Max. Contact drop, initial		150mV			150mV				
Contact drop after life test		175mV			175mV				
Continuous current		350A			500A				
Overload		2400A - 1sec / 800A -	60sec / 600A - 3	300sec	4000A - 1sec / 1000A - 20sec				
Rupture current		3500A			5000A				
Auxiliary contacts		Continuous current 8A	/ Make and Brake	e 16A					
Call Data		12\\DC		24 / 20	VDC				
Coil Data		9-16VDC		<b>24 / 28</b> 18-32V[					
Voltage range									
Nominal voltage Pick up voltage max.		12VDC 9VDC		24/28V 18VDC					
Drop out voltage Coil resistance		≤ 4VDC 20Ω ± 10%		≤ 7VDC 82Ω ± 10					
Coil current max.									
Con current max.		0.60A		0.35 / 0	J.40A				
Rated contact load (24/28	VDC)	350A		500A					
Resistive load		50.000 cycles - 350A		50.000 cycles - 500A					
Mechanical Life		100.000 cycles - 85A		100.00	0 cycles - 125A				
Operating times NO	Cont	act	Operating times	s	NC Contact				
<b>Operate</b> ma	x. 25r	nsec	Break time		max. 20msec				
<b>Bounce</b> ma	x. 5m	sec	Make time inc. bounce		max. 40msec				
Release ma	x. 80r	nsec							


## **Available Types**

	Type Ordering key	Contact		UNC	Side	2-hole bot-	4-hole bot-	Suppression	Polarity	Auxiliary	Weight
		NO	NC	threads	mounting	tom mount.	tom mount.	device	protection	contact	kg/pound
24V / 28V 350A	2606.01	Х			Х			Х	Х		1.20 / 2.70
	2606.03	X			Х			Х	Х	Х	1.20 / 2.70
	2606.11	Х				Х		Х	Х		1.25 / 2.80
	2606.13	X				X		×		Х	1.25 / 2.80
	2606.21	X					Х	×	X		1.30 / 2.90
12V 500A	2605.251	X			Х			Х			1.20 / 2.70
24V / 28V 500A	26.05.01	X			Х			×	X		1.20 / 2.70
	26.05.03	Х			Х			Х	Х	Х	1.20 / 2.70
	26.05.11	X				Х		Х	Х		1.25 / 2.80
	26.05.21	X					X	X	X		1.30 / 2.90
	26.05.51	X			Х			Х			1.20 / 2.70
	26.05.52	X		X	Х			Х			1.20 / 2.70
	26.05.61	X				X		X			1.25 / 2.80
	26.05.62	X		X		Х		Х			1.25 / 2.80
	26.05.63	X				Х		Х		Х	1.25 / 2.80
	26.05.71	X					X	×			1.25 / 2.80
	26.25.01		Х		Х			Х	Х	Х	1.20 / 2.70
	26.25.11		X			X		Х	X	Х	1.20 / 2.70
	26.25.21		X				X	X	X	Х	1.25 / 2.80

Other types and customer specified types upon request


## **Circuits**

#### NO-Contact




#### NO-Contact

with auxiliary contact




#### NO-Contact

with auxiliary contact and polarity protection




#### **NO-Contact**

with polarity protection




## NO-Contact

with auxiliary contact and polarity protection




## NO-Contact UNC-version

with US-Termination





## **Accessories**




## **Technical drawings**


#### Side mounting







#### 2-hole bottom mounting







#### Side mounting NO-Contact with auxiliaries





#### 4-hole bottom mounting





TE Connectivity, TE, TE connectivity (logo), KISSLING (logo) and KISSLING (word) are trademarks owned or licensed by the TE Connectivity family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2020 TE Connectivity | All Rights Reserved. K1166689 | Version 12/2020