

H ABOUT US ▼

76053

Products > Switches > Pressure Switches > Standard Pressure Switches > 5000 Series > 76053

Overview

5000 Series pressure switch with standard terminal These switches sense a change in the pressure, opening or closing an electrical circuit when the designated set point is reached. Honeywell S&C View More



Technical Specifications

Operating Pressure	250 psi	Product Type	Pressure Switch
Connector(s)	1/8-27 NPT	Contact	25 psi to 50 psi, ±5 psi
Standard Factory Set Points	25 psi, 30psi, 35 psi, 38 psi, & 40 psi	Setting Range	
		Electrical Termination	#8-32 screw
Circuitry	NO	Contact(s)	Silver alloy,
Proof Pressure	500 psi		gold plated
		Burst Pressure	1250 psi

View More

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
PDF HP, HE, MH, ME, LP, and LE Series Pressure Switches Datasheet	Datasheet	English	3MB
Series 5000 Extended Duty Pressure Switch Datasheet	Datasheet	English	120KB
Application Note: Honeywell Pressure Switches, HP-HE- ME-LP-LE Series	Application Note	English	1MB
Sensors and Switches in Mobile Cranes	Application Note	English	194KB

View More

Product Features

- Stands up to extended duty applications
- Factory set, capable of field adjustment
- Direct acting blade gold-plated contacts
- · No dead band
- · Kapton diaphragm for compatibility with a variety of fluids
- Various electrical connections and terminations
- Optional rubber boot

Applications

- · Engine transmission
- Hydraulics and brakes





support







•



- Power steering
- Fuel pressure
- ABS brakes
- Cruise control
- Oxygen concentrators
- Dental air
- Embalming equipment
- Generators/compressors
- Pool/spa water pressure

NAVIGATION LINKS DISTRIBUTOR LINKS

HOME DIGITAL U-HML

PRODUCTS ECOM LOGIN

INDUSTRIES REQUEST ACCESS TO ECOM

CONTACT US SALES/AD PORTAL LOGIN

NEWS & EVENTS SALES/AD PORTAL ACCESS REQUEST

ABOUT US SAMPLE REQUEST

LEVDNING TITID LOCK

LANGUAGE

English

SITE INFORMATION

PRIVACY STATEMENT

TERMS & CONDITIONS

This site uses cookies to simplify and improve your usage and experience of this website. Cookies are small text files stored on the device you are using to access this website. If you ignore this message and continue without changing your browser settings, we will assume that you are consenting to our use of cookies. For further information on our use of cookies, please set Don't show this message again