



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **2**

Number of Rows: **1**

Features

Product Type Features

PCB Connector Assembly Type	PCB Mount Header
Connector System	Board-to-Board
Header Type	Breakaway
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Connector Contact Load Condition	Fully Loaded
PCB Mount Orientation	Vertical
Number of Positions	2
Number of Rows	1
Board-to-Board Configuration	Parallel

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Mating Square Post Dimension	.64 mm[.025 in]
	100 – 200 μin
PCB Contact Termination Area Plating Material Finish	Matte
Contact Shape & Form	Square



Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Copper Alloy
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Material Thickness	.381 μm[15 μin]
Contact Type	Pin
Contact Current Rating (Max)	3 A

Termination Features

Square Termination Post & Tail Dimension	.64 mm[.025 in]
Termination Post & Tail Length	2.29 mm[.09 in]
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

Mating Alignment	Without
PCB Mount Retention	Without
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	2.54 mm[.1 in]
Housing Material	LCP (Liquid Crystal Polymer), LCP-GF (Liquid Crystal Polymer)

Dimensions

PCB Thickness (Recommended)	1.6 mm[.063 in]
-----------------------------	-----------------

Usage Conditions

Housing Temperature Rating	High
Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Approved Standards	CSA LR7189, UL E28476
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	500
--------------------	-----



Packaging Type

Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Pin-in-Paste capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-881545-1 AMP SHUNT ASS'Y	 TE Part # 880584-1 SHUNT CONNECTOR	 TE Part # 881545-1 SHUNT LP W/HANDLE 2POS 15AU	 TE Part # 1-382811-6 SHUNT,ECON,PHBR 15AU,BLACK L/P
---	--	---	--



TE Part # 1-382811-8
SHUNT,ECON,PHBR 5AU, BLACK L/P



TE Part # 382811-8
SHUNT, ECON, PHBR 5AU, BLACK



TE Part # 382811-2
SHUNT, ECON, PHBR15 AU, BLUE



TE Part # 382811-6
SHUNT, ECON, PHBR 15 AU,BLACK



TE Part # 390088-2
BLACK HSG WITH 15AU CONTACT




TE Part # 382811-9
SHUNT, ECON, PHBR 15AU, RED



TE Part # 1-880584-1
SHUNT CONN. ASS'Y



TE Part # 2-880584-1
SHUNT CONN. ASSY



TE Part # 390088-6
YELLOW HSG WITH 15AU CONTACT



TE Part # 880584-5
SHUNT CONNECTOR


Also in the Series | [AMPMODU Headers](#)



PCB Connector Mounting(1)



PCB Connector Shrouds(1)



PCB Headers & Receptacles(6333)



PCB Latches, Locks & Retainers(2)



Wire-to-Board Connector Assemblies
& Housings(5)




Wire-to-Board Connector Contacts(66)

Customers Also Bought






TE Part #182647-1
11-4 CPC PLUG



TE Part #5650951-5
ASSY,PIN,EUROCARD,TYPE C,LEAD-




TE Part #282841-4
TERMI-BLOK PCB MOUNT 4P. 5



TE Part #60619-1
CMNL SOK PTPBR L/P



TE Part #1586514-2
03P CMNL HDR ASSY PC NATL LF



TE Part #282857-9
TERMI-BLOK PCB MOUNT 90 9P.5



TE Part #1-480303-0
03P CMNL PLUG HSG F/H NATL



TE Part #4-1393224-9
RY211024



TE Part #1546306-3
3P .374" DR BARRIER STRIP

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-146284-2_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5-146284-2_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-146284-2_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

TE Material Declaration

English