



HONEYWELL  
PART NUMBER  
**21SM144**  
PRODUCT CODE  
TXK4400

REV	DOCUMENT	CHANGED BY	CHECK
6	0038111	PK 20MAY08	ASD



**NOTE-**  
 1- MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX. DIA. ON .375±.002 CENTERS.  
 2- TERMINALS ARE PLATED FOR SOLDERING.  
 3- SWITCH WILL WITHSTAND TEMPERATURE OF 250°F.

RELEASE NO.	SR - 7570
REPLACES	-

CHARACTERISTICS	
OPERATING FORCE	--- 3 OZ MAX
RELEASE FORCE	--- 1 OZ MIN
DIFFERENTIAL TRAVEL	--- .002 MAX
OVERTRAVEL	--- .005 MIN

ELECTRICAL DATA		
CONTACT ARRANGEMENT SPDT		
30 VOLTS DC RATING		
	SEA LEVEL	50,000 FT
INDUCTIVE	3 AMP	2.5 AMP
RESISTIVE	5 AMP	5 AMP
MAXIMUM INRUSH 24 AMP		
APPROVALS	KEMA, CE	5A, 250V ~ T85 1E4
	UL, CSA	5A, 250 VAC

DESIGN UNITS: INCH
TOLERANCES UNLESS NOTED:
NO PLACE X ±
ONE PLACE .X ±
TWO PLACE .XX ±
THREE PLACE .XXX ±
FOUR PLACE .XXXX ±
ANGLES ±
THIRD ANGLE PROJECTION

DRAWN	VK	17OCT07
CHECK	RJ	17OCT07
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
RASTER		

<b>Honeywell</b>			
TITLE <b>SWITCH - BASIC</b>			
SIZE	TYPE	DRAWING NAME	REV
<b>B</b>	<b>I</b>	<b>21SM144</b>	<b>6</b>
SCALE	-	WEIGHT .006 LB MAX	SHEET 1 OF 1