



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.82 – 2.08 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Terminates To	Wire & Cable
Wire Stop	No
Wire/Cable Type	Regular Wire
Insertion Force	Low
Sealable	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Pre-Tin
Crimp Type	F-Crimp



Barrel Type	Open
-------------	------

Mechanical Attachment

Mating Retention Type	Dimple
Extraction Force	7 – 100 Newton
Wire Insulation Support	With

Dimensions

Accepts Wire Insulation Diameter Range	2.21 – 3.4 mm [.087 – .134 in]
Overall Length	21.2 mm [.834 in]
Receptacle Terminal Stock Thickness	.41 mm [.016 in]
Wire Size	.82 – 2.08 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C [-40 – 230 °F]

Industry Standards

UL Rating	Recognized
-----------	------------

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece/Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2232343-1 250 PL EX FLAG REC. 18-12AWG PTBR	 TE Part # 175022-2 250 POSITIVE REC EX MK-2	 TE Part # 2232343-2 250 PL EX FLAG REC. 18-12AWG PTBR FLAT	 TE Part # 2376579-2 250 FASTON PCB TAB TPBR
 TE Part # 2376582-2 250 FASTON PCB TAB TPBR	 TE Part # 2376591-2 250 FASTON PCB TAB TPBR	 TE Part # 2376595-2 250 FASTON PCB TAB TPBR	 TE Part # 174817-1 POSITIVE LOCK 250 (6.3 MM) SLEEVE
 TE Part # 174817-2 250 sleeve PL YELLOW transparent	 TE Part # 234619-1 DAHT P L EX & EX II 18-14 ASSY	 TE Part # 2376591-3 250 FASTON PCB TAB TPBR LP	

Also in the Series | Positive Lock 250



Automotive Terminals(1)



Crimp Terminal Housings(202)



Insertion & Extraction Tools(3)



Insulation Boots & Sleeves(6)



Quick Disconnects(189)

Customers Also Bought



TE Part #2-316132-3
Header Assembly: Wire-to-Board, 15A, gold or tin plated



TE Part #9-1609095-1
5FB3=F8363



TE Part #170038-2
187 FASTON,REC.,20-16 AWG,TPBR




TE Part #1-480424-0
04P CMNL PLUG HSG F/H NATL




TE Part #1744037-4
04P EC PWR.200 CL HDR ASSY VRT



TE Part #170823-2
250 FASTON SLEEVE,REC., TRANSPARENT



TE Part #172774-4
MIC MK-II LP



TE Part #172776-1
MIC MARK-2 REC CONTACT L.P

Documents

Product Drawings

PL 250 RECEPTACLE 18-14 AWG PTBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_175023-1_O.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_175023-1_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_175023-1_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Positive Lock Mk-III .250 Series](#)

English

Product Specification

English

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English

[POSITIVE LOCK EX CONTACT](#)

English