



TE Internal #: 8-55856-3


Ring Terminals & Spade Terminals, Ring Tongue, 12 – 10 AWG

Wire Size, 2.62 – 6.64 mm² Wire Size, 5180 – 13100 CMA Wire Size,

Stud Size M4 / #8

[View on TE.com >](#)

Terminals & Splices > Ring Terminals & Spade Terminals



Ring & Spade Terminal Type: **Ring Tongue**

Wire Size: **5180 – 13100 CMA**

Stud Size: **#8, M4**

Features

Product Type Features

Shape Description	RING-088
Stud Size	#8, M4
Sealable	Yes
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Terminal Angle	180 °
----------------	-------

Electrical Characteristics

Voltage (Max)	1000 V, 600 V
---------------	---------------

Contact Features

Ring & Spade Terminal Type	Ring Tongue
Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------



Dimensions

Wire Size	5180 – 13100 CMA
Stud Diameter	4.17 mm[.164 in]
Tongue Thickness	1.07 mm[.042 in]
Overall Product Length	35.76 mm[1.405 in]
Accepts Wire Insulation Diameter (Max)	6.1 mm[.24 in]
Accepts Wire Insulation Diameter Range	6.1 mm[.24 in]

Usage Conditions

Insulation Option	Partially Insulated
Operating Temperature Range	125 °C[257 °F]

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin
Heavy Duty	Yes

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	25
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 55856-1
12-10 PRE-INSUL SEALED TERM R

TE Part # 55893-1
CRIMP.TOOL 22-10(SEALED PROD.)

TE Part # 55894-1
CRIMP.TOOL 16-8 (SEALED PROD.)

Customers Also Bought



TE Part #T4141012121-000
M12,REAR MOUNT,FEMALE,A,12P, SOLDER PCB



TE Part #5-747904-2
9 Plug Solder Cup, Gold Flash,




TE Part #1825255-1
MHS12204=SPDT SL SW VERT AG




TE Part #5103308-3
A/L LOW PRO HDR 16P VERT BLACK



TE Part #102387-3
16 MODIV HSG COMP DR .100 POL



TE Part #284391-2
TERMI-BLOK PCB SIDE ENTRY STAC



TE Part #284391-3
TERMI-BLOK PCB SIDE ENTRY STAC

Documents

Product Drawings
12-10 PRE-INSUL SEALED TERM R

English

CAD Files



Customer View Model

[ENG_CVM_CVM_8-55856-3_G.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_8-55856-3_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_8-55856-3_G.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English