



Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: Hood

Cable Entry Location: Side

Hood & Base Locking Device Type: Locking Clip

Sealable: Yes

Circuit Application: Power & Signal

Features

Product Type Features

Product Size	8
Hood & Base Connector Product Type	Hood
Sealable	Yes

Body Features

Material	Die Cast Aluminum
Cable Entry Location	Side

Mechanical Attachment

Screw & Hole Thread Size	PG29
Hood & Base Locking Device Type	Locking Clip

Usage Conditions

Corrosion Protected	Yes
---------------------	-----

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # T1500243000-000 H24B-AG-LB	 TE Part # T3609290101-000 DLX-29-MS	 TE Part # T1660243129-000 H24B-SDRH-LB-PG29	 TE Part # T2040242101-000 HE-024-M
 TE Part # T1010241500-000 H24B-KDTP-LB	 TE Part # T1650243129-000 H24B-SGRH-LB-PG29	 TE Part # T1650243229-000 H24B-SGRH-LB-2PG29	 TE Part # T1660243129-100 H24B-SDRHM-LB-PG29



TE Part # T1660243229-000
H24B-SDRH-LB-2PG29

TE Part # T1660243229-100
H24B-SDRHM-LB-2PG29

Also in the Series | HDC IP65

Rectangular Connector Hoods & Bases
(1258)

Customers Also Bought

TE Part #T1510482000-000
H48B-AD-LB

TE Part #T1270242129-000
H24B-TSBH-PG29

TE Part #T1329160116-000
H16A-TG-PG16

TE Part #T2040242201-000
HE-024-F

TE Part #T2040242101-000
HE-024-M

TE Part #T1280242129-000
H24B-TGBH-PG29

TE Part #T1320484040-000
H48B-TG/TS-RO-M40/M40

TE Part #T1510243100-000
H24B-ADM-LB

TE Part #S2100124101-000
HK6/6-012-M 10-25,2.5

TE Part #S2100124201-000
HK6/6-012-F 10-25,2.5



Documents

Product Drawings
H24B-TSH-RO-PG29

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_T1330240129-000_A.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_T1330240129-000_A.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_T1330240129-000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
Heavy Duty Connectors

English

HEAVY DUTY CONNECTORS

English

Product Specifications
Application Specification

English