




Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Hood**

Cable Entry Location: **Side**

Hood & Base Locking Device Type: **Screwlock**

Sealable: **Yes**

Features

Product Type Features

Product Size	3
Hood & Base Connector Product Type	Hood
Sealable	Yes

Body Features

Material	Die Cast Aluminum
Cable Entry Location	Side

Mechanical Attachment

Locking Device Location	Housing
Screw & Hole Thread Size	M25
Hood & Base Locking Device Type	Screwlock

Usage Conditions

Corrosion Protected	Yes
---------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # T1932060000-000
H6BPR-AGC

TE Part # T1932060001-000
H6BPR-AGC

Customers Also Bought

TE Part #1-1827875-3
DYNAMIC 1200D HDR ASSY V 6P X
BLACK GOLD

TE Part #1-175195-5
DYNAMIC D-3 REC CONT/M PRE-TIN

TE Part #350764-4
12P UMNL HDR ASSY PC

TE Part #350761-4
04P UMNL HDR ASSY PC



TE Part #316454-1
M-U-M-N-L PLUG CABLE CLAMP



TE Part #1-770834-0
MINI UMNL SOK AU LF



TE Part #T1500163000-000
H16B-AG-LB



TE Part #T2020011015-000
DDM-1.5



TE Part #T2020012010-000
DDF-1.0



TE Part #T2020012015-000
DDF-1.5

Documents

Product Drawings

H6BPR-TSHC-M25

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_T1912060125-000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_T1912060125-000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_T1912060125-000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

HEAVY DUTY CONNECTORS

English

Product Specifications

Application Specification

English

Application Specification