

**TOOLCRAFT****SAFETY DATA SHEET**

according to Regulation (EC) No 1907/2006 (REACH) and Regulation (EU) 2020/878

**TOOLCRAFT Anaerobe Klebstoffe
Kennzeichnungsfrei**

Material number Anaerobe Kennzeichnungsfrei

Revision date: 30.11.2023
Version: 2.0
Replaces version: 1.2
Language: en-DE
Date of print: 26.2.2024

Page: 1 of 8

SECTION 1: Identification of the substance/mixture and of the company/undertaking**1.1 Product identifier**

Trade name: TOOLCRAFT Anaerobe Klebstoffe Kennzeichnungsfrei

This safety data sheet pertains to the following products:

2730833: TOOLCRAFT SCHRAUBENS. HOCHFEST 50 ML kennzeichnungsfrei
2731303: TOOLCRAFT SCHRAUBENS. MITTELFEST 50 ML Kennzeichnungsfrei
2731304: SCHRAUBENSICHERUNG HOCHFEST 10 ML kennzeichnungsfrei
886524: TOOLCRAFT SCHRAUBENSICHERUNG MITTELFEST 10 ML**1.2 Relevant identified uses of the substance or mixture and uses advised against**

General use: Adhesive, sealant

1.3 Details of the supplier of the safety data sheetCompany name: Conrad Electronic SE
Street/POB-No.: Klaus-Conrad-Str.1
Postal Code, city: 92240 Hirschau
Germany
WWW: www.conrad.de
E-mail: quality-control@conrad.de
Telephone: +49 (0)9604/40 8988
Telefax: +49 (0)9604/40 8936

Department responsible for information:

Telephone: +49 (0) 9604/40-8988, E-mail: quality-control@conrad.de

1.4 Emergency telephone number

Telephone: +49(0) 89-19240

SECTION 2: Hazards identification**2.1 Classification of the substance or mixture****Classification according to EC regulation 1272/2008 (CLP)**

This mixture is classified as not hazardous.

2.2 Label elements**Labelling (CLP)**

Hazard statements: not applicable

Precautionary statements: not applicable

2.3 Other hazards

Special danger of slipping by leaking/spilling product.

Endocrine disrupting properties, Results of PBT and vPvB assessment:

No data available

SECTION 3: Composition/information on ingredients

3.1 Substances: not applicable

3.2 Mixtures

Chemical characterisation: Mixture of the substances listed below with non-hazardous additions:

**TOOLCRAFT****SAFETY DATA SHEET**

according to Regulation (EC) No 1907/2006 (REACH) and Regulation (EU) 2020/878

**TOOLCRAFT Anaerobe Klebstoffe
Kennzeichnungsfrei**

Material number Anaerobe Kennzeichnungsfrei

Revision date: 30.11.2023
Version: 2.0
Replaces version: 1.2
Language: en-DE
Date of print: 26.2.2024

Page: 2 of 8

Hazardous ingredients:

Identifiers	Designation Classification	Content
REACH 01-2119529241-49-xxxx EC No. 248-258-5 CAS 27138-31-4	Oxydipropyl dibenzoate Aquatic Chronic 3; H412.	< 15 %
REACH 01-2119489379-17-xxxx EC No. 236-675-5 CAS 13463-67-7	Titanium dioxide Carc. 2; H351.	< 1 %

Full text of H- and EUH-statements: see section 16.

Additional information: Contains Silicon dioxide. The maximum workplace exposure limits are, where necessary, listed in section 8.

SECTION 4: First aid measures**4.1 Description of first aid measures**

In case of inhalation: Move victim to fresh air; if necessary, provide artificial respiration or oxygen. Make sure he/she is warm and comfortable. Seek medical treatment in case of troubles.

Following skin contact: Immediately clean with water and soap followed by thorough rinsing. Take off contaminated clothing and wash it before reuse. In case of skin reactions, consult a physician.

After eye contact: Immediately flush eyes with plenty of flowing water for 10 to 15 minutes holding eyelids apart. Remove contact lenses, if present and easy to do. Continue rinsing. In case of eye irritation consult an ophthalmologist.

After swallowing: Rinse mouth immediately and drink plenty of water. Do not induce vomiting. Never give anything by mouth to an unconscious person. Seek medical attention.

4.2 Most important symptoms and effects, both acute and delayed

No data available

4.3 Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures**5.1 Extinguishing media**

Suitable extinguishing media: Water spray jet, foam, extinguishing powder, carbon dioxide.

Extinguishing media which must not be used for safety reasons:
Full water jet**5.2 Special hazards arising from the substance or mixture**Combustible. May form dangerous gases and vapours in case of fire.
Furthermore, there may develop: Hydrogen fluoride, nitrogen oxides, sulphur oxides, carbon monoxide and carbon dioxide.**5.3 Advice for firefighters**

Special protective equipment for firefighters:

Wear self-contained positive pressure breathing apparatus and full firefighting protective clothing.

Additional information:

Move undamaged containers from immediate hazard area if it can be done safely. Do not allow fire water to penetrate into surface or ground water. Use water spray jet to minimise or disperse vapours.

**SECTION 6: Accidental release measures****6.1 Personal precautions, protective equipment and emergency procedures**

Provide adequate ventilation. Avoid breathing mist/vapours/spray. Wear appropriate protective equipment. Take off contaminated clothing and wash it before reuse. Avoid contact with skin and eyes. Keep unprotected people away.

6.2 Environmental precautions

Do not allow to enter into ground-water, surface water or drains.

6.3 Methods and material for containment and cleaning up

Soak up with absorbent materials such as sand, siliceus earth, acid- or universal binder. Store in special closed containers and dispose of according to ordinance.

Additional information: Special danger of slipping by leaking/spilling product.

6.4 Reference to other sections

Refer additionally to section 8 and 13.

SECTION 7: Handling and storage**7.1 Precautions for safe handling**

Advices on safe handling: Provide adequate ventilation, and local exhaust as needed. Avoid contact with skin and eyes. Avoid breathing mist/vapours/spray. Wear appropriate protective equipment. Take off contaminated clothing and wash it before reuse. When using do not eat, drink or smoke. Wash hands thoroughly after handling.

Precautions against fire and explosion: Keep away from heat. When handling larger quantities, take precautionary measures against electrostatic charging.

7.2 Conditions for safe storage, including any incompatibilities

Requirements for storerooms and containers: Keep container dry, tightly closed and store at cool and aired place. Keep only in original container. Storage temperature: < 20 °C. Protect from heat and direct sunlight.

Hints on joint storage: Do not store together with acids, peroxides, copper or strong oxidizing agents. Keep away from food, drink and animal feedingstuffs.

Storage class: 10 = Combustible liquids, unless storage class 3

7.3 Specific end use(s)

No information available.

SECTION 8: Exposure controls/personal protection**8.1 Control parameters**

Occupational exposure limit values:

CAS No.	Designation	Type	Limit value
7631-86-9	Silicon dioxide	Germany: DFG Kurzzeit	1,6 mg/m ³ (respirable fraction)
		Germany: DFG Langzeit	0,02 mg/m ³ (respirable fraction)
		Germany: TRGS 900 Langzeit	4 mg/m ³ (inhalable fraction)
13463-67-7	Titanium dioxide	Germany: DFG Kurzzeit	2,4 mg/m ³ multipliziert mit der Materialdichte (respirable fraction)
		Germany: DFG Langzeit	0,3 mg/m ³ multipliziert mit der Materialdichte (respirable fraction)



DNEL/DMEL: Information about Oxydipropyl dibenzoate:
DNEL Long-term, workers, systemic, inhalative: 8,8 mg/m³
DNEL Long-term, workers, systemic, dermal: 10 mg/kg bw/d
DNEL Short-term, workers, systemic, inhalative: 35,08 mg/m³
DNEL Short-term, workers, systemic, dermal: 170 mg/kg bw/d
DNEL Long-term, consumer, systemic, inhalative: 8,69 mg/m³
DNEL Long-term, consumer, systemic, dermal: 2,5 mg/kg bw/d
DNEL Long-term, consumer, systemic, oral: 5 mg/kg bw/d
DNEL Short-term, consumer, systemic, inhalative: 8,7 mg/m³
DNEL Short-term, consumer, systemic, dermal: 80 mg/kg bw/d
DNEL Short-term, consumer, systemic, oral: 80 mg/kg bw/d

PNEC: Information about Oxydipropyl dibenzoate:
PNEC water (freshwater): 0,02 mg/L
PNEC water (marine water): 0,002 mg/L
PNEC sediment (freshwater): 8,03 mg/kg dw
PNEC sediment (marine water): 0,803 mg/kg dw
PNEC soil: 1 mg/kg dw
PNEC sewage treatment plant: 10 mg/L
PNEC oral: 333 mg/kg Food

8.2 Exposure controls

Provide good ventilation and/or an exhaust system in the work area.

Personal protection equipment

Occupational exposure controls

Respiratory protection: Respiratory protection must be worn whenever the WEL levels have been exceeded.
Particulates filter P2 according to EN 143.
The filter class must be suitable for the maximum contaminant concentration (gas/vapour/aerosol/particulates) that may arise when handling the product.

Hand protection: Protective gloves according to DIN EN 374.
Glove material: Nitrile rubber
Layer thickness: > 0,56 mm
Breakthrough time: < 8 h
Observe glove manufacturer's instructions concerning penetrability and breakthrough time.

Eye protection: Tightly sealed goggles according to DIN EN ISO 16321-1:2022.

Body protection: Wear suitable protective clothing.

General protection and hygiene measures:
Avoid breathing mist/vapours/spray. Take off contaminated clothing and wash it before reuse.
Wash hands thoroughly after handling. When using do not eat, drink or smoke. Avoid contact with skin and eyes.

Environmental exposure controls

Refer to "6.2 Environmental precautions".

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Physical state at 20 °C and 101.3 kPa	liquid
Colour:	varying, depends on colouring
Odour:	characteristic
Odour threshold:	No data available
Melting point/freezing point:	No data available
Initial boiling point and boiling range:	No data available
Flammability:	No data available
Upper/lower flammability or explosive limits:	No data available
Flash point/flash point range:	> 60 °C
Decomposition temperature:	No data available
pH:	No data available



Viscosity, kinematic:	No data available
Solubility:	No data available
Partition coefficient: n-octanol/water:	No data available
Vapour pressure:	No data available
Density:	No data available
Vapour density:	No data available
Particle characteristics:	Not applicable

9.2 Other information

Explosive properties:	No data available
Oxidizing characteristics:	No data available
Auto-ignition temperature:	No data available
Evaporation rate:	No data available
Additional information:	No data available

SECTION 10: Stability and reactivity

10.1 Reactivity

Refer to subsection "Possibility of hazardous reactions".

10.2 Chemical stability

Stable under recommended storage conditions.

10.3 Possibility of hazardous reactions

Exothermic polymerization may occur.

10.4 Conditions to avoid

Do not expose to temperatures above 15 °C.
Avoid high temperatures or direct sunlight.

10.5 Incompatible materials

Acids, peroxides, copper, strong oxidizing agents.

10.6 Hazardous decomposition products

	No decomposition when used properly.
Thermal decomposition:	No data available



SECTION 11: Toxicological information

11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008

Toxicological effects: Acute toxicity (oral): Lack of data.
Acute toxicity (dermal): Lack of data.
Acute toxicity (inhalative): Lack of data.
Skin corrosion/irritation: Lack of data.
Serious eye damage/irritation: Lack of data.
Sensitisation to the respiratory tract: Lack of data.
Skin sensitisation: Lack of data.
Germ cell mutagenicity/Genotoxicity: Lack of data.
Carcinogenicity: Lack of data.
Reproductive toxicity: Lack of data.
Effects on or via lactation: Lack of data.
Specific target organ toxicity (single exposure): Lack of data.
Specific target organ toxicity (repeated exposure): Lack of data.
Aspiration hazard: Lack of data.

11.2 Information on other hazards

Endocrine disrupting properties: No data available
Other information: No data available

SECTION 12: Ecological information

12.1 Toxicity

Aquatic toxicity: Information about Oxydipropyl dibenzoate:
Fish toxicity: Pimephales promelas (fathead minnow)
LC50: 3,7 mg/L/96h
NOEC: 1,2 mg/L/96h
Daphnia toxicity: Daphnia magna (Big water flea)
EL50: 19,3 mg/L/48h
Algae toxicity: Pseudokirchneriella subcapitata (green algae)
EL50: 1,1 mg/L/72h
Water Hazard Class: 2 = obviously hazardous to water

12.2 Persistence and degradability

Further details: No data available

12.3 Bioaccumulative potential

Partition coefficient: n-octanol/water:
No data available

12.4 Mobility in soil

No data available

12.5 Results of PBT and vPvB assessment

No data available

12.6 Endocrine disrupting properties

No data available

12.7 Other adverse effects

General information: Do not allow to enter into ground-water, surface water or drains.

**TOOLCRAFT****SAFETY DATA SHEET**

according to Regulation (EC) No 1907/2006 (REACH) and Regulation (EU) 2020/878

**TOOLCRAFT Anaerobe Klebstoffe
Kennzeichnungsfrei**

Material number Anaerobe Kennzeichnungsfrei

Revision date: 30.11.2023
Version: 2.0
Replaces version: 1.2
Language: en-DE
Date of print: 26.2.2024

Page: 7 of 8

SECTION 13: Disposal considerations**13.1 Waste treatment methods****Product**

Waste key number: 08 04 10 = waste adhesives and sealants other than those mentioned in 08 04 09
Recommendation: Dispose of waste according to applicable legislation.
Do not dispose of with household waste.
Do not empty into drains.

Package

Recommendation: Dispose of waste according to applicable legislation. Handle contaminated packages in the same way as the substance itself.

SECTION 14: Transport information**14.1 UN number or ID number**

ADR/RID, IMDG, IATA-DGR: not applicable
ADN: ID 9003

14.2 UN proper shipping name

ADR/RID, IMDG, IATA-DGR: Not restricted
ADN: ID 9003, SUBSTANCES WITH A FLASH-POINT ABOVE 60 °C AND NOT MORE THAN 100 °C

14.3 Transport hazard class(es)

ADR/RID, IMDG, IATA-DGR: not applicable
ADN: Class 9, Code: M12

14.4 Packing group

ADR/RID, ADN, IMDG, IATA-DGR:
not applicable

14.5 Environmental hazards

Dangerous for the environment: Substance/mixture is not environmentally hazardous according to the criteria of the UN model regulations.
Marine pollutant - IMDG: no

14.6 Special precautions for user**Inland waterway craft (ADN)**

Hazard label: -
Transport permitted: T
Equipment necessary: PP

14.7 Maritime transport in bulk according to IMO instruments

No data available

SECTION 15: Regulatory information**15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture****National regulations - Germany**

Storage class: 10 = Combustible liquids, unless storage class 3
Water Hazard Class: 2 = obviously hazardous to water
Technical guidance air: 5.2.5
Further regulations, limitations and legal requirements:
No data available

**TOOLCRAFT**

SAFETY DATA SHEET

according to Regulation (EC) No 1907/2006 (REACH) and Regulation (EU) 2020/878

TOOLCRAFT Anaerobe Klebstoffe Kennzeichnungsfrei

Material number Anaerobe Kennzeichnungsfrei

Revision date: 30.11.2023
Version: 2.0
Replaces version: 1.2
Language: en-DE
Date of print: 26.2.2024

Page: 8 of 8

National regulations - EC member states

Further regulations, limitations and legal requirements:

No data available

15.2 Chemical Safety Assessment

For this mixture a chemical safety assessment is not required.

SECTION 16: Other information

Wording of the H-phrases under paragraph 2 and 3:

H351 = Suspected of causing cancer.

H412 = Harmful to aquatic life with long lasting effects.

Reason of change:

Changes in section 2: Labelling

Changes in section 3: Composition / Information on ingredients

General revision

Date of first version:

5.11.2021

Department issuing data sheet: see section 1: Department responsible for information

Abbreviations and acronyms:

ADN: European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways

ADR: European Agreement concerning the International Carriage of Dangerous Goods by Road

Aquatic Chronic: Hazardous to the aquatic environment - chronic

AS/NZS: Australian Standards/New Zealand Standards

Carc.: Carcinogenicity

CAS: Chemical Abstracts Service

CFR: Code of Federal Regulations

CLP: Classification, Labelling and Packaging

DMEL: Derived minimal effect level

DNEL: Derived no-effect level

EC: European Community

EL50: Effective loading rate 50%

EN: European Standard

EQ: Excepted quantities

EU: European Union

IATA: International Air Transport Association

IATA-DGR: International Air Transport Association – Dangerous Goods Regulations

IBC Code: International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk

IMDG Code: International Maritime Dangerous Goods Code

LC50: Median lethal concentration

MARPOL: Maritime Pollution: The International Convention for the Prevention of Pollution from Ships

NOEC: No Observed Effect Concentration

OEL: Occupational Exposure Limit Value

OSHA: Occupational Safety and Health Administration

PBT: Persistent, bioaccumulative and toxic

PNEC: Predicted no-effect concentration

REACH: Registration, Evaluation, Authorisation and Restriction of Chemicals

RID: Regulations Concerning the International Carriage of Dangerous Goods by Rail

TLV: Threshold Limit Value

TRGS: Technical Rules for Hazardous Substances

vPvB: Very persistent and very bioaccumulative

WEL: Workplace Exposure Limit

The information in this data sheet has been established to our best knowledge and was up-to-date at time of revision. It does not represent a guarantee for the properties of the product described in terms of the legal warranty regulations.