

1418887-1 ✓ ACTIVE

AMP | MQS


TE Internal #: 1418887-1

Automotive Terminals, Receptacle, Mating Tab Width .025 in [.63 mm], Tab Thickness .025 in [.63 mm], Locking Lance, MQS

[View on TE.com >](#)



Terminals & Splices > Automotive Terminals > MQS, RECEPTACLE AND TAB



Terminal Type: **Receptacle**

Mating Tab Width: **.63 mm [.025 in]**

Mating Tab Thickness: **.63 mm [.025 in]**

Terminal Transmits: **0 – 24 A (Low Power)**

Sealable: **No**

[All MQS, RECEPTACLE AND TAB \(125\)](#)

Features

Product Type Features

Receptacle Style	180°
Sealable	No
Primary Locking Feature	Locking Lance

Contact Features

Contact Size	.63mm
Contact Fabrication	Stamped & Formed
Typical Current Rating	7.5 A
Crimp Type	FFC
Terminal Type	Receptacle
Mating Tab Width	.63 mm[.025 in]
Mating Tab Thickness	.63 mm[.025 in]
Interface Plating	Tin (Sn)
Contact Termination Area Plating Material	Tin (Sn)



Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

Dimensions

Wire Insulation Diameter	.2 mm[.01 in]
--------------------------	---------------

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C, 140 °C, 145 °C, 150 °C [176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F][284 °F][293 °F][302 °F]
Operating Temperature Range	-40 – 150 °C[-40 – 302 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Packaging Features

Packaging Method	Reel
Packaging Quantity	12500

Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1-528013-1
FFC PISTOL GRIP HAND TOOL CASE




TE Part # 5-528441-3
FFC APPLICATOR MQS TERMINALS


Also in the Series | MQS




Automotive Connector Caps & Covers (133)



Automotive Connector EMC Shielding (2)




Automotive Connector Locks & Position Assurance (29)




Automotive Housings (492)




Automotive Seals & Cavity Plugs (26)



Automotive Terminals (96)



Insertion & Extraction Tools (42)



Other Automotive Connector Accessories (13)



PCB Headers & Receptacles(209)

Customers Also Bought



TE Part #487526-3
004 HOUSING FFC RCPT 100CL SR



TE Part #1452128-1
MQS, RECEPTACLE AND TAB



TE Part #770005-3
UMNL II PIN PHBZ, PRE-TIN



CRIMPER REPRESENTATION ONLY

TE Part #2077758-2
INSULATION CRIMPER




TE Part #2151344-2
OCEAN_2.0_APPLICATOR-S-062F091O




TE Part #2318822-1
5POS,5.8X0.8,TAB INNER HSG



TE Part #5053146049
RNF-100-3/8-0-25MM



TE Part #2308422-1
HSD,90+2MQS REC,CAB ASSY



TE Part #8-1372712-1
Cutting Blade

Documents

Product Drawings

MQS0,63 Sn rec LL unseal. FFC

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1418887-1_A_c-1418887-1-a.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1418887-1_A_c-1418887-1-a.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1418887-1_A_c-1418887-1-a.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Micro Quadlok Interconnection System \(MQS\)](#)

English

Product Specifications

[Application Specification](#)

English