



New Cosy+ Range

Pick up the right Internet Connectivity

Ewon Cosy+ WiFi

The Ewon Cosy+ is an industrial VPN gateway designed to offer secure remote access across the Internet, to machines and equipment at customers' sites or in the field.

Cosy+ WiFi is the ideal product to be sure to have a successful connection in all situations.

Local Wireless access connectivity to ease troubleshooting and maintenance task of engineers working into a factory around the machine.



Key Benefits

EASIER THAN EASY	Straightforward setup, to make any machine IIoT-ready in a matter of minutes. Easy device maintenance with firmware upgrade for Talk2M Pro customers. Non-intrusive outbound connections, requiring no change on the existing network. Reach your equipment in 2 clicks, wherever it is.
NO HIDDEN COSTS	Start immediately with a free Talk2M account, supporting an unlimited number of devices and users. Connect from any device, with the free desktop, web and mobile apps.
IT APPROVED	Trusted chain from Hardware to the Cloud: <ul style="list-style-type: none">• Hardware Root Of Trust brings security to the core of the hardware.• Secure Element, the perfect place to store crucial secrets.• Birth certificate to prevents cloning and counterfeiting.• Secure boot sequence ensuring that only code signed by Ewon is executed.• Restrictive list of most secured cypher suites to protect the communications with Talk2M. Proven security posture: <ul style="list-style-type: none">• Certified ISO 27001 & cybersecurity partnership with NVISO.• Solution based on the latest open standard technologies. Manage the connectivity of all your machines and collaborators from one place.
READY TO USE AND RELIABLE	20+ data centers spread worldwide for coverage and maximal business continuity. Global and reliable infrastructure, with an extensive Service Level Agreement. Scalability: add at any time as many devices and users as you need. Email & SMS relay services, to receive notifications from your machine. Secondary WAN interface for backup Internet Connectivity

PLC Connectivity

Remote access possibilities:

Using the Ewon Cosy, you can remotely connect to your PLC using its Ethernet port or its USB interface.

USB device support depends on the compatibility between the USB driver used on the PC and the Talk2M USB integration.

In principle, all PLC models with an Ethernet port are supported.

Below is a non-exhaustive list of some of the compatible devices for major PLC brands:

Rockwell Automation/Allen Bradley	SLC5/500 Series (over Eth) Micro/Compact/Control Logix Series (over Eth/USB)
Siemens	S7-200/300/400/1200/1500 (over Eth)* Logo (over Eth)
Schneider Electric	TSX Series (over Eth) M Series (M258, M340, ...) (over Eth/USB)
Mitsubishi Electric	iQ-R, iQ-F series (over Eth) Q, F, L series (over Eth)
VIPA	Speed 7 series (over Eth)
OMRON	C, CJ, CP, CS Series (over Eth/USB) NJ, NX Series (over Eth/USB)
HITACHI	EH Series
KEYENCE	KV series
Yokogawa	e-RT3 series, FA-M3V series

*remote access to safety PLC devices (-F series) is not supported

Technical Specifications

WAN Connectivity	Ethernet or WiFi: 802.11 a/b/g/n.
Frequencies	Channels: 1 to 11(inclusive).
Security	Client : WPA, WPA2 and WEP. Access Point : WPA2.
Antenna Connector	RP-SMA female connector.
Antenna	Included in the delivery. Antenna covering the ISM band for WLAN system 802.11 a/b/g/n. The antenna has SMA connector and can be tilted 90 degrees. <ul style="list-style-type: none"> • Client : frequency and gain: 2.4GHz / 2.0dBi max and 5 GHz /4.5dBi max.; impedance: 50 Ohms. • Access point : frequency: 2.4GHz; gain: 2.0dBi max; impedance: 50 Ohms
WAN Ethernet	up to 3 ports,10/100 Mb Ethernet.
LAN Ethernet	up to 4 ports,10/100 Mb Ethernet.
Field interface	Up to 10 USB 2.0 connections, female connector 2.0.
SD Card reader	YES, for Cosy commissioning (firmware upgrade, backup, Talk2M registration).
Router	IP filtering, IP forwarding, NAT, Port forwarding, Proxy, Routing table, DHCP client/server.

Internet	Outbound connection for Talk2M through port TCP 443 (and optionally port UDP 1194).
VPN Tunneling	OpenVPN either in SSL UDP or TCP.
Talk2M	Talk2M Free+ or Talk2M Pro, natively supported.
VPN Security	Communications between the remote user and the Ewon are fully encrypted using the SSL/TLS protocol, thereby ensuring data authenticity, integrity & confidentiality. All users and Ewon units are authenticated using x509 SSL certificates and end-to-end traffic is encrypted using strong symmetric & asymmetric algorithms that are part of the SSL/TLS protocol cipher suite.
Synchronization	Embedded real-time clock, manual setup via the web interface or automatic via NTP.
File Management	FTP server for configuration, firmware update.
Web-based configuration	Embedded web interface with setup wizards for configuration and maintenance (no additional software needed). Basic authentication (login/password) and session control for security.
Mechanicals	Dimensions: 108,80 x 99 x 43,60 mm (H x D x W). DIN rail or wall screw fixing system.
Weight	214 gr.
Power supply	12-24 VDC +/-20%, LPS.
Temperature Range	Operating: -25°C to +60°C, 10 to 95% relative humidity (non-condensing). Storage: -30°C to +70°C, 10 to 95% relative humidity (non-condensing).
Hardware	1xDO: open drain (MOSFET) 200mA; isolation 1.5kV, 2xDI: 0 to 24VDC; 1.5 kV isolation.
Marking	CE, cULus, FCC, UKCA, Japan, RCM
Warranty	36 months


Certifications

Type tests	<p>Temperature - Operating & Storage tested according to:</p> <p>IEC 60068-2-1 Cold test IEC 60068-2-2 Dry heat test IEC 60068-2-14 Change of temperature IEC 60068-2-30 Cyclic damp heat test</p> <p>Vibration & shocks tested according to:</p> <p>IEC 60068-2-27 Bumps IEC 60068-2-64 Vibration (broad-band random) IEC 60068-2-6 Vibration (sinusoidal)</p>
CE	<p>Compliant with:</p> <p>EMC directive 2014/30/EU (Immunity: industrial level) ROHS2 2011/65/EU directive with amendment 2015/863 REACH regulation</p>
UKCA	<p>Compliant with:</p> <p>Electromagnetic Compatibility Regulations 2016; The Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012.</p>

FCC/IC	This product complies with the Part 15 of the FCC rules.
Other	RCM for Australia, New Zealand, WPC India.
Safety	The product fulfils the requirements of: EN 62368-1:2014 + A11:2017 UI 62368-1 Second Edition CAN/CSA C22.2 No. 62368-1-14 Second Edition

WiFi Access Point

Local Wireless access connectivity to ease troubleshooting and maintenance task of engineers working into a factory around the machine.



File

Version

Size

Read online

Ordering Information

ORDER CODE: EC7133J_00MA

MODEL NUMBER: 04002

WARRANTY: 3 years

For purchasing instructions and terms and conditions, see: [How to buy](#)

Do you want the advice of our experts? [Contact Us](#)

✓ Cosy 131 Range

Pick up the right Internet Connectivity

