


## Data Sheet

---

### Cat6a S/FTP Installation Solid Cable BC 23AWG/1 LSZH 500 MHz, CPR, Orange



#### Drawing:



BN	Length (m)	Cable Color
2752210	100	Orange
2752211	305	Orange

#### Application

10 BASE-T (IEEE 802.3)

4/16 Mbps TOKEN RING (IEEE 802.5)

100 BASE-VG-AnyLAN

100 Mbps TP-PMD (ANSI X3T9.5)

100 BASE-T (IEEE 802.3)

55/155 Mbps ATM

1000 BASE-T (Gigabit Ethernet)

1.2 Gbps ATM

10G BASE-T

## Data Sheet

---

### Reference Standard

ISO/IEC 11801, EN 50173, ANSI/TIA-568.2-D

IEC 61156-5

EN 50288-10-1

EN 50575

EN 50399

Low smoke (IEC 61034)

Halogen free (IEC 60754-1/2)

Flame retardant (IEC60332-1-2)

CPR-Dca s2, d1, a1 Verified

ROHS 2.0 &amp; REACH Compliant

3P Certified

### Technical Data

Structure	Construction	S/FTP
	Number of Pairs	4 Pairs
Conductor	AWG	23
	Conductor material	99.99% oxygen-free copper
	Conductor dimension	1/0.55±0.008 mm
Insulation	Insulation material	FMPE
	Insulation dimension	1.35±0.05 mm
	Number color (Ring or stripe or pure marking)	1.White-Blue & Blue 2.White-Orange & Orange 3.White-Green & Green 4.White-Brown & Brown
Cabling	Twisting lay length	≤30 mm
	Cabling lay length	≤200 mm
Filler	Filler material	N/A
Binder	Binder material	N/A
Shield	Individual shield & material	AL-Foil
	Primary overall shield & material	AL-MG braid
	Secondary overall shield & material	N/A
	Shield coverage approx.	40%
	Drain wire	N/A

## Data Sheet

Outer Jacket	Jacket material	LSZH
	Jacket thickness nominal	0.50 mm
	Overall nominal dimension	7.60±0.30 mm
	Jacket rip cord	None
Mechanical Characteristics	Operating temperature range	-20 °C ~ +75 °C
	Installation temperature range	0 °C ~ +50 °C
	Bulk cable weight approx.	-
	Max. recommended pulling tension	110 N
	Min. bend radius (install)	8 x O.D.
	Outer jacket tensile strength	≥9.0 MPa
	Outer jacket elongation	≥100%
	Outer jacket aging condition	100 °C x 168 hrs
	After aging, tensile strength	≥70% of Unaging
	After aging, elongation	≥50% of Unaging
	Cold bend (static)	No Crack (@ -20 °C x 4 hrs)
Electrical Characteristics	Nom. mutual capacitance	≤5.6 nF/100 m (@1 kHz)
	Pair to ground capacitance unbalance	≤160 pF/100 m
	Nominal velocity of propagation	72%
	Max. delay skew	25 ns/100 m
	Max. conductor DC resistance	9.5 Ω/100 m (@2 °C)
	Max. conductor resistance unbalance	2% (@ 20 °C) within a pair
	Min. insulation resistance	5000 MΩ.km
	Max. operating voltage - UL	300 V
	Dielectric strength	2.5 kV DC for 2 s
	(Conductor/conductor, conductor/screen)	1.0 kV DC for 1 min

## Data Sheet

---

### Electrical Characteristics

Frequency	Attenuation	NEXT	PSNEXT	Return loss	ELFEXT	PSELFEXT
(MHz)	(dB/ 100m)	(dB)	(dB)	(dB)	(dB)	(dB)
4	3.5	64.1	61.8	23.0	56.0	53.0
8	5.0	59.4	57.0	24.5	49.9	46.9
10	5.5	57.8	55.5	25.0	48.0	45.0
16	7.0	54.6	52.2	25.0	43.9	40.9
20	7.8	53.1	50.7	25.0	42.0	39.0
25	8.8	51.5	49.1	24.3	40.0	37.0
31.25	9.8	50.0	47.5	23.6	38.1	35.1
62.5	14.0	45.1	42.7	21.5	32.1	29.1
100	18.0	41.8	39.3	20.1	28.0	25.0
200	26.1	36.9	34.3	18.0	22.0	19.0
250	29.5	35.3	32.7	17.3	20.0	17.0
350	35.6	31.8	29.1	17.3	17.1	14.1
500	43.8	26.7	23.8	17.3	14.0	11.0