




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **1600 – 4100 CMA**

Mating Tab Width: **6.35 mm [.25 in]**

Features

Product Type Features

Terminates To	Wire & Cable
Wire Stop	No
Wire/Cable Type	Regular Wire
Insertion Force	Low
Sealable	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm [.25 in]
Mating Tab Thickness	.81 mm [.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp



Barrel Type	Open
-------------	------

Mechanical Attachment

Mating Retention Type	Dimple
Wire Insulation Support	With

Dimensions

Accepts Wire Insulation Diameter Range	3.05 – 4.32 mm [.12 – .17 in]
Receptacle Terminal Stock Thickness	.41 mm [.016 in]
Wire Size	1600 – 4100 CMA

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 125 °C [-40 – 125 °F]

Packaging Features

Packaging Quantity	10000
Packaging Method	Strip/Reel

Other

Line	FASTON .250
------	-------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)












EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these

limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 520987-1 250 FASTON HSG. REC 4P BLACK</p>	 <p>TE Part # 280232-8 250 FASTON POST INS.,REC.,1 POS, NATRUAL</p>	 <p>TE Part # 520987-2 250 FASTON HSG. REC 4P NATURAL</p>	 <p>TE Part # 1738494-1 250 FASTON HSG.,REC.,NATRUAL</p>
 <p>TE Part # 521069-1 250 FASTON HSG. REC 14.9MM2P NATURAL</p>	 <p>TE Part # 521066-1 250 FASTON HSG. REC 4P BLACK</p>	 <p>TE Part # 2-735075-6 250 FASTON INS POST.,REC.,1 POS, NATRUAL</p>	 <p>TE Part # 1738472-1 FASTON SWITCH NYLON NAT</p>
 <p>TE Part # 735075-5 250 FASTON HSG. REC. 1P BLACK</p>	 <p>TE Part # 1738475-1 250 FASTON HSG.,REC.,NATRUAL</p>	 <p>TE Part # 1-480416-8 250 FASTON HSG.,REC.,1 POS, NATRUAL</p>	 <p>TE Part # 1-735075-5 250 FASTON INS POST.,REC.,1 POS, BLACK</p>
 <p>TE Part # 521053-1 250 FASTON HSG. REC 1P NATURAL</p>	 <p>TE Part # 280232-6 250 FASTON POST INS.,REC.,1 POS, NATRUAL</p>	 <p>TE Part # 280232-5 250 FASTON POST INS.,REC.,1 POS, BLACK</p>	 <p>TE Part # 521065-1 250 FASTON HSG. REC 4P BLACK</p>



TE Part # 1-1969232-1
250 FASTON HSG., REC., 2 POS,
NATURAL



TE Part # 1-1969232-3
250 FASTON HSG., REC., 2 POS,
YELLOW




TE Part # 1-1969232-4
250 FASTON HSG., REC., 2 POS, GREEN




TE Part # 1-520987-4
250 FASTON HSG., REC., 4 POS, BLACK


Also in the Series | FASTON 250



Compression Connectors(4)




Crimp Terminal Housings(141)




Insertion & Extraction Tools(6)



Magnet Wire Terminals(1)



PCB Terminals(144)



Quick Disconnects(453)



Splices(4)

Customers Also Bought



TE Part #521367-2
ULTRA-POD 250 ASSY REC 18-14
AWG TPBR



TE Part #964202-1
STD TIMER CONTACT



TE Part #42452-2
187 FASTON REC 20-16 AWG TPBR



TE Part #928247-3
3P ST-TIMER GEH



TE Part #521282-2
ULTRA-POD 250 ASSY REC 18-14
AWG TPBR



TE Part #521599-2
ULTRA-POD 187 ASY REC 18-14 TPBR



TE Part #2238155-1
POS LOCK 250 Rec, MKII, 18-14 TPBR



TE Part #2238207-3
187 FASTON, REC., 20-16 AWG, TPBR



Documents

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2238196-3_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2238196-3_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2238196-3_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1-1773948-2 Standard Line FASTON Receptacles QRG](#)

English

Product Specifications

[Product Specification](#)

English

[FASTON, .250 STD. REC. TEST REPORT](#)

English

Product Environmental Compliance

[MD_2238196-3_02272018559_dmtec](#)

English

[MD_2238196-3_02272018559_dmtec](#)

English