


86/125 & 86/128

high elastic



Properties	Unit	86/125	86/128
Colour		dark orange	pink / dark orange
Assembly		single layer, fibre glass reinforcement up to 4.0 mm	double layer carrier film 86/52 in 0.125 mm

Thermal Properties

Thermal resistance R_{th}	K/W	0.8	0.8
Thermal impedance R_{ti}	$^{\circ}\text{Cmm}^2/\text{W}$	322	322
	Kin^2/W	0.5	0.5
Thermal conductivity λ	W/mK	1.5	1.5

Electrical Properties

Breakdown voltage $U_{d; ac}$	kV	6.0	6.0
Dielectric breakdown $E_{d; ac}$	kV/mm	12.0	12.0
Volume resistivity	Ωm	6.1×10^{10}	1.8×10^{12}
Dielectric loss factor $\tan \delta$		1.5×10^{-1}	1.0×10^{-3}
Dielectric constant ϵ_r		4.3	2.3

Mechanical Properties

Measured thickness (+/-10%)	mm	0.500	0.500
Hardness	Shore 00	10 - 25	10 - 25
Young's modulus	N/cm ²	24	67

Physical Properties

Application temperature	$^{\circ}\text{C}$	-40 to +180	-40 to +180
Density	g/cm ³	2.0	1.9
Total mass loss (TML)	Ma.-%	< 0.29	< 0.29
Flame rating	UL-94	V-0	V-0*

Possible thickness details see page 58

*KERAFOLE® test according to UL

SOFTTHERM® 86/125 has an improved thermal performance without influencing the dielectric and mechanical properties. 86/125 is a single layer, supported with fibre glass reinforcement.

Data for engineer guidance only. Observed performance varies in application. Engineers are reminded to test the material in application.

NOTE:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. KERAFOL® is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. All specifications are subject to change without notice. Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded. In case KERAFOL® would be nevertheless held liable, on whatever legal ground, KERAFOL®'s liability will in no event exceed the amount of the concerned delivery. All KERAFOL® products are sold pursuant to the KERAFOL®'s Terms and Conditions of sale and delivery in effect from time to time, a copy of which will be furnished upon request.

01-2019