

# KERN FEJ 17K-4M



High-capacity precision balance with password-protected user administration, also with EC type approval [M]



Pattern approval for conformity assessment	✓
Accuracy classe	II
Verification scale interval [e]	1 g
Verification scale interval [e] (ct)	5 ct

## Display

Display type	LCD
Display digit height	16,5 mm
Display backlight	✓
Display screen size	172×58 mm
Languages of the user interface	English

## Construction

Dimension display device (W×D×H)	290×180×60 mm
Dimension housing (W×D×H)	350×520×170 mm
Dimensions weighing platform (W×D×H)	400×350×150 mm
Dimensions weighing surface (W×D)	350×400 mm
Material housing	stainless steel, cast iron
Material display housing	stainless steel
Material weighing plate	stainless steel
Material platform	Stainless steel
Stand height	710 mm
Wall mount	✓
Display device cable length	1 m
Levelling feet adjustable	✓

## Functions

Number of keys for operation	9
Capacity display	✓
PreTare function	✓
Tare function	manual (multi)
Percentage determination	✓
Counting function	✓
Tolerance weighing	✓
Underfloor weighing	Hook (optional)
Interfaces	Digital I/O (optional, factory) RS-232 standard - 2x
IP protection - complete device	IP65
IP protection - display	IP65
IP protection - load cell	IP65
IP protection - platform	IP65

## Category

Brand	KERN
Product category	Laboratory balances
Product group	Precision balances

## Measuring System

Readability [d]	0,1 g
Readability carat [d] (ct)	0,5 ct
Weighing capacity [Max]	17000 g
Minimum weight [Min] (ct)	25 ct
Weighing capacity [Max] (ct)	85000 ct
Eccentric loading at 1/3 [Max]	0,3 g
Minimum weight [Min]	5 g
Reproducibility	0,1 g
Linearity	± 0,3 g
Weighing system	Tuning fork
Resolution	170.000
Tare range	17000 g
Units	kg g dwt tl (Tw) tl (HK) ozt tl (Singap, Malays) ct lb oz tol
Units (if device is conformity assessed)	kg g ct
Default unit	g
Stabilization time	3 s
Warm-up time	120 min
Adjustment options	Internal calibration (automatic)

## Approval

CE mark	✓
Conformity assessment possible ex works	✓

# KERN FEJ 17K-4M



High-capacity precision balance with password-protected user administration, also with EC type approval [M]

## Counting

Smallest piece weight when piece counting - laboratory conditions	100 mg
Smallest piece weight when piece counting - normal conditions	1 g
Reference quantity	5, 10, 30, 50, 100, n (any number of pieces)
Counting resolution (laboratory conditions)	170.000

## Power Supply

Input voltage power supply / power [Max]	100 V - 240 V AC, 50 / 60 Hz
Input voltage device / power [Max]	12 V, 1.0 A
Plug-in power supply type	Power adapter
Supplied plug-in power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO AUS UK US
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
Rechargeable battery charging time	12 h
Rechargeable battery operating time - backlight off	10 h

## Environmental conditions

Humidity of environment [Max]	80 %
Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C

## Packing & Shipping

Readability force [d] (N)	1 d
Shipping method	Parcel service
Dimensions packaging (W×D×H)	490×830×430 mm
Net weight approx.	19 kg
Gross weight approx.	26 kg

## Services (optional)

Article number for conformity assessment	965-217
Article number for DAkkS calibration	963-128

## Piktogramme

### STANDARD



### OPTION



### FACTORY

